

[See all 71 Products in Family](#)

Basler ace acA4024-8gm Monochrome GigE Camera

See More by [Basler](#)



Basler ace GigE Cameras



Stock **#37-207** [CONTACT US](#)

[Similar Cameras](#)

-

1

+

£399⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£399.00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

Monochrome

Spectrum:

General

Monochrome Camera

Type:

Model Number:

acA4024-8gm	
Basler	Manufacturer:
ace	Camera Series:
Physical & Mechanical Properties	
42 x 29 x 29 (excludes connectors and lens mount)	Dimensions (mm):
90	Weight (g):
Full	Housing:
Sensor	
1/1.7"	Sensor Format:
12.00	Resolution (Megapixels):
8.00	Frame Rate (fps):
4,024 x 3,036	Pixels (H x V):
1.85 x 1.85	Pixel Size, H x V (µm):
7.44 x 5.62	Sensing Area, H x V (mm):
Sony IMX226	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Rolling	Shutter Type:
10/12 bit	Pixel Depth:
Programmable via camera API	Exposure Time:
70.4	Dynamic Range (dB):
GigE Vision, GenICam	Machine Vision Standard:
Electrical	
2.5 (12VDC External Power Supply) 2.9 (PoE)	Power Consumption (W):
Hardware & Interface Connectivity	
GigE (PoE)	Interface:
GigE, RJ45 with Screw Locks	Connector:
Power Supply Required and Sold Separately: USA: #68-466 Europe: #68-466 Japan: #68-466 Korea: #68-466 China: #68-466	Power Supply:
1 opto-coupled input line, 1 opto-coupled output line, 1 general purpose I/O (GPIO) line	GPIOs:
Hardware Trigger (GPIO), Software Trigger, or Free-Run	Synchronization:
Back Panel	Interface Port Orientation:
6-pin Hirose (HR10)	GPIO Connector Type:
Threading & Mounting	
C-Mount	Mount:
1/4-20 with Tripod Mount Adapter #88-517	Mounting Threads:
Environmental & Durability Factors	
	Operating Temperature (°C):

0 to +50	
	Storage Temperature (°C):
-20 to +80	

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:


Compliant	Reach 235:
-----------	------------

Product Details

- Perfect Analog Replacement
- Ultra-Small Form Factor
- Power Over Ethernet (PoE)
- Includes Basler Pylon Driver

Basler ace GigE Cameras are economical Gigabit Ethernet cameras that provide an ideal upgrade opportunity for analog camera users. With a small form factor matching that of many analog cameras (29 x 29mm), the ace can be a drop-in replacement to an existing analog system or a great choice to start a new project. Basler ace GigE Cameras can use Power Over Ethernet (PoE) (2 GigE cables required). The cameras can have long cable lengths and are the optimal choice for use on a factory floor. All cameras include the industry-proven Basler Pylon SDK Software and Driver.

Technical Information



MT9P031 Sensor QE Curve