

TECHSPEC[®] f/2, 12mm Focal Length Green Series M12 Lens



12mm Focal Length, #54-854

Stock **#54-854** 20+ In Stock

-

1

+

£70⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-49	£70.00 each
Qty 50+	£56.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Green Series	Series:
M12 Imaging Lens	Type:
No	IR Cut Filter:
Standard Lens	Imaging Lens Type:

Physical & Mechanical Properties	
Fixed	Iris Option:
19.50	Length (mm):
16	Maximum Diameter (mm):
16	Outer Diameter (mm):
6	Weight (g):
Optical Properties	
	Horizontal Field of View @ Max Sensor Format: 80.5mm - 30.1°
	Field of View at Max Sensor Format: Horizontal: 80.5mm - 30.1° Vertical: 60mm - 22.7° Diagonal: 101.5mm - 37.5°
	Horizontal Field of View, 1/2" Sensor: 80.5mm - 30.1°
	Horizontal Field of View, 1/2.5" Sensor: 72.7mm - 27.4°
	Horizontal Field of View, 1/3" Sensor: 60.0mm - 22.7°
	Horizontal Field of View, 1/4" Sensor: 44.9mm - 17.1°
150 lp/mm @20% Contrast	Resolution:
8.00	Maximum Image Circle (mm):
0.0191	Numerical Aperture NA, Object Side:
5(5)	Number of Elements (Groups):
400 - 700	Wavelength Range (nm):
12.00	Focal Length FL (mm):
150 - ∞	Working Distance (mm):
f/2	Aperture (f/#):
-2.2 @ Full Field	Distortion (%):
7.1 - 6.75	Back Focal Length BFL (mm):
λ/4 MgF ₂ @ 580nm	Coating Specification:
7.50	Entrance Pupil Position (mm):
10.41	Object Space Principal Plane (mm):
-3.73	Image Space Principal Plane (mm):
-2.2	Maximum Distortion (%):
-7.56	Exit Pupil Position (mm):
VIS	Lens Wavelength Range:
Sensor	
1/2"	Maximum Sensor Format:
8.30	Pixel Size (μm):
Threading & Mounting	
N/A	Filter Thread:
M12 x0.5	Mounting Threads:

S-Mount (M12 x0.5)	Mount:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

Optimized Working Distance: 150 - 250mm

- Up to 1/2", S-Mbunt Lens
- Up to 0.4 MegaPixels, 8.3µm Pixel Size Sensors
- Board Camera Lens Optimized for Close WD and Finite Conjugate
- 6mm to 25mm Focal Lengths


TECHSPEC® Green Series M12 Lenses designed for use in compact and board level cameras provide excellent image quality in a small, versatile package. Optimized to cover 1/3" and 1/2" sensor formats and weighing only a few grams, these machine vision lenses meet the most demanding space and weight restrictions. Each lens is threaded for M12 x0.5, except the 25.0mm focal length option ([#54-855](#)). TECHSPEC® Green Series M12 Lenses are ideal for wide angle and close focus applications, large area inspect for the automotive, forensic, pharmaceutical, and food industries. Prescription data is available by submitting a [Request for Prescription Form](#).

Note: Compatible [TECHSPEC M12 Imaging Lens Accessories](#) available.


Edmund Optics has created multiple product families of our TECHSPEC® M12 S-Mount Lenses, which are designed to provide high resolution. These high performance lenses feature precision glass designs in a metal housing and have optimized specifications between each product family to meet your application needs.

- Blue Series M12 Lenses:** High resolution finite conjugate designs optimized for machine vision working distances.
- Rugged Blue Series M12 Lenses:** [Stabilized ruggedization](#) versions of our Blue Series M12 Lenses, utilizing the same optics.
- Green Series M12 Lenses: Finite conjugate designs optimized for machine vision working distances.
- Red Series M12 Lenses:** Infinite conjugate designs optimized for high resolution performance out to infinity.
- HEO Series M12 Lenses:** Harsh Environment Optics (HEO) sealed versions of our Red Series M12 Lenses.
- Liquid Lens M12 Lenses:** Integrated liquid lens for fast electronic focus.


Technical Information




#54-854, f/2, 12mm Focal Length Green Series M12 Lens, Distortion Plot




#54-854, f/2, 12mm Focal Length Green Series M12 Lens, Relative Illumination Plot



#54-854, f/2, 12mm Focal Length Green Series M12 Lens, Working Distance versus Field of View Plot




#54-854, f/2, 12mm Focal Length Green Series M12 Lens, Modulated Transfer Function (MTF) Plot, 250mm Working Distance, f2



#54-854, f/2, 12mm Focal Length Green Series M12 Lens, Depth of Field Plot, 250mm Working Distance, f2

Focal Length	A	B	C**	D	Mounting Thread
6.00	14.0	11.70	4.0 - 3.9	3.5	M12 x0.5
8.00	14.0	20.40	8.9 - 8.7	6.0	M12 x0.5
12.00	16.0	19.50	7.1 - 6.75	6.0	M12 x0.5
25.00	18.0	24.40	12.6 - 11.9	9.0	M16 x0.5



**Minor adjustment required to match WD limits.