

TECHSPEC f/2.5, Visible, 3.6mm HEO Series M12 Lens



3.6mm Focal Length

Stock #58-841 **15 In Stock**

⊖ 1 ⊕ £128.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-49	£128.00 each
Qty 50+	£100.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

HEO Series **Product Family:**

M12 Imaging Lens **Type:**

No **IR Cut Filter:**

Meets IEC IPX7 and IPX9K **Imaging Lens Type:**

Physical & Mechanical Properties

Fixed	Iris Option:
14.10	Length (mm):
14	Maximum Diameter (mm):
14	Outer Diameter (mm):
4	Weight (g):

Optical Properties

Horizontal Field of View @ Max Sensor Format:
725.0mm - 84.1°

Field of View at Max Sensor Format:
Horizontal: 725.9mm - 84.2°
Vertical: 469.9mm - 60.5°
Diagonal: 1240.8mm - 114.4°

Horizontal Field of View, 1/3" Sensor:
725.0mm - 84.1°

Horizontal Field of View, 1/4" Sensor:
469.3mm - 60.5°

Maximum Image Circle (mm):
6.00

Numerical Aperture NA, Object Side:
0.0018

Resolution, On-Axis:
100 lp/mm @20% Contrast

Number of Elements (Groups):
4(3)

Wavelength Range (nm):
425 - 675

Focal Length FL (mm):
3.60

Working Distance (mm):
400 - ∞

Aperture (f#):
f/2.5

Distortion (%):
-45.62 @ Full Field

Back Focal Length BFL (mm):
4.69 - 4.67

Coating Specification:
425 - 625nm BBAR

Entrance Pupil Position (mm):
2.67

Object Space Principal Plane (mm):
5.08

Image Space Principal Plane (mm):
1.77

Maximum Distortion (%):
-45.62

Exit Pupil Position (mm):
-5.72

Lens Wavelength Range:
VIS

Sensor

1/3"	Maximum Sensor Format:
5.00	Pixel Size (μm):

Threading & Mounting

N/A	Filter Thread:
S-Mount (M12 x 0.5)	Mount:

Environmental & Durability Factors

IPX7 and IPX9K	Environmental Rating:
----------------	------------------------------

Type of Ruggedization:
Waterproof (IPX7 and IPX9K)

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Up to 1/2", S-Mount Lens
- Up to 1.2 MegaPixels, 5µm Pixel Size Sensors
- Meets IEC Ingress Protection Ratings of IPX7 and IPX9K
- 2.2mm to 8mm Focal Length


TECHSPEC® HEO Series M12 Lenses integrate high performance optics into a sealed, ruggedized enclosure. Designed to meet IEC Ingress Protection Codes IPX7 and IPX9K, these lenses withstand exposure to water up to 1 meter depth for 30 minutes and operate in close-range high-pressure, high-temperature water spray downs. Threaded for M12 x 0.5, these lenses are optimized for 1/3" and 1/2" sensor formats. Each HEO Series Lens is waterproof, dustproof, and fog proof with the ability to be hermetically sealed to a camera. TECHSPEC® HEO Series M12 Lenses are ideal for harsh environment applications, such as automotive. Prescription data is available by submitting a [Request for Prescription Form](#)

Note: Compatible [TECHSPEC® M12 Imaging Lens Accessories](#) available.


Edmund Optics has created multiple product families of our TECHSPEC® M12 S-Mount Lenses, which are designed to provide high resolution. These high performance lenses feature precision glass designs in a metal housing and have optimized specifications between each product family to meet your application needs.

- **Blue Series M12 Lenses:** High resolution finite conjugate designs optimized for machine vision working distances.
- **Rugged Blue Series M12 Lenses:** [Stabilized ruggedization](#) versions of our Blue Series M12 Lenses, utilizing the same optics.
- **Green Series M12 Lenses:** Finite conjugate designs optimized for machine vision working distances.
- **Red Series M12 Lenses:** Infinite conjugate designs optimized for high resolution performance out to infinity.
- HEO Series M12 Lenses: Harsh Environment Optics (HEO) sealed versions of our Red Series M12 Lenses.
- **Liquid Lens M12 Lenses:** Integrated liquid lens for fast electronic focus.


Technical Information




#58-841, f/2.5, Visible, 3.6mm HEO Series M12 Lens, Distortion Plot




#58-841, f/2.5, Visible, 3.6mm HEO Series M12 Lens, Relative Illumination Plot




#58-841, f/2.5, Visible, 3.6mm HEO Series M12 Lens, Working Distance versus Field of View Plot




#58-841, f/2.5, Visible, 3.6mm HEO Series M12 Lens, Modulated Transfer Function (MTF) Plot, 600mm Working Distance, f2.5



#58-841, f/2.5, Visible, 3.6mm HEO Series M12 Lens, Depth of Field Plot, 600mm Working Distance, f2.5



#58-841, f/2.5, Visible, 3.6mm HEO Series M12 Lens, Modulated Transfer Function (MTF) Plot, 3600mm Working Distance, f2.5



#58-841, f/2.5, Visible, 3.6mm HEO Series M12 Lens, Depth of Field Plot, 3600mm Working Distance, f2.5

Focal Length	A	B	C	D
2.2mm	21.0mm	16.4mm	2.2mm	5.4mm
3.6mm	14.0mm	14.1mm	4.5mm	4.5mm
8.0mm	14.0mm	15.0mm	8.7mm	4.0mm