

[See all 2 Products in Family](#)

FLIR C3-X Compact Thermal Imaging Camera



Stock **#75-072** NEW **2 In Stock**

-

1

+

£483^{.65}

ADD TO CART

Volume Pricing	
Qty 1+	£483.65 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

Measurement Tools:	
Spotmeter; box with min./max	
Standard Measurement Temperature (°C):	
-20 to 300°C (-4 to 572°F)	
Spectrum:	
Thermal	

General

Operating Lifetime (hours):	
4 hours	
Model Number:	

Cx Series	
53.6°	Field of View (°):
Contents of Kit: Thermal Camera, USB Cable, Wrist Strap Lanyard, Carrying Pouch, Printed Documentation	
Operating Modes: Infrared image, Visual image, MSX, Picture-in-picture (IR area on visual image)	
Physical & Mechanical Properties	
138 × 84 × 24 mm (5.4 × 3.3 × 0.94 in)	Dimensions (mm):
0.19 kg (0.42 lb)	Weight (g):
0 to 100°C (32 to 212°F): ±3°C (±5.5°F); 100 to 300°C (212 to 572°F): ±3% [ambient temp. 15 to 35°C (59 to 95°F) and object temp. above 0°C (32°F)]	Accuracy (%):
2 m (6.6 ft)	Drop Test:
Optical Properties	
5 MP	Resolution:
8–14 μm	Spectral Range:
Focus free	Focus Range (mm):
Iron, Gray, Rainbow, Rainbow HC	Color:
Performance	
128 × 96 (12,288 pixels)	Thermal Resolution (Pixels):
Thermal: 0.1 m (0.32 ft), MSX: 0.3 m (0.98 ft)	Minimum Focus Distance (m):
Electrical	
8.7 Hz	Frequency (Hz):
<70 mK	Sensitivity (W²):
120	Charging Time (minutes):
Rechargeable built-in Lithium ion battery	Battery Type:
Hardware & Interface Connectivity	
USB-C (1 A)	Connector:
Threading & Mounting	
Tripod: UNC ¼"-20 (built-in)	Mount:
Environmental & Durability Factors	
-10 to 50°C (14 to 122°F)	Operating Temperature (°C):
-40 to 70°C (-40 to 158°F)	Storage Temperature (°C):
Camera housing and lens: IP54 rated (IEC 60529)	Environmental Rating:
Additional Info	
Emissivity, matte/semi-matte/semi-gloss + custom value, Reflected apparent temperature, Atmospheric compensation	Measurement Correction:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Compact, Lightweight Thermal Imagers for Field Use
- Touchscreen Interface with Built-in Flashlight and Point-and-Shoot Operation
- Durable, Drop-Tested, and Waterproof Design
- Wi-Fi for fast Sharing and Reporting

The FLIR CxSeries delivers compact, easy-to-use thermal imaging for industrial inspections, maintenance, and troubleshooting. With touchscreen operation, built-in flashlights, and rugged, drop-tested designs, these cameras are built for durability and fast on-the-job use. The C3-X(128 × 96 resolution) offers an affordable option for quick diagnostics and basic troubleshooting, while the C5 (160 × 120 resolution) provides greater image detail and higher temperature range for more advanced inspections. Both models feature built-in Wi-Fi for quick image sharing and reporting directly from the field. Lightweight, portable, and simple to operate, the CxSeries is ideal for technicians who need reliable thermal imaging that fits easily into daily workflows.

Mdel	C3-X	C5
Resolution	128 × 96 (12,288 pixel)	160 x 120 (19,200 pixel)
Temp Range	-20 to 300°C (-4 to 572°F)	-20 to 400°C (-4 to 752°F)
Thermal sensitivity	<0.07°C	<0.07°C

Accuracy: At ambient temp. 15°C to 35°C (59°F to 95°F) and object temp. above 0°C (32°F), 0°C to 100°C (32°F to 212°F): ±3°C (±5.5°F); 100°C to 300°C (212°F to 572°F): ±3%

;