

[See all 93 Products in Family](#)

# Basler ace2 a2A5060-4gcBAS Color GigE Basic Camera

See More by [Basler](#)



Basler ace2 GigE Cameras (Front)



Stock #74-976 [CONTACT US](#)

- 1 + £1,396<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	£1,396.00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

## Product Downloads

Color **Spectrum:**

## General

Color Camera **Type:**

a2A5060-4gcBAS **Model Number:**

Basler **Manufacturer:**

Ace2 **Camera Series:**

## Physical & Mechanical Properties

**Dimensions (mm):**  
55.5 x 29 x 29 mm (without lens mount or connectors)

100 **Weight (g):**

Full **Housing:**

## Sensor

1.1" **Sensor Format:**

25.00 **Resolution (Megapixels):**

4.00 **Frame Rate (fps):**

5,060 x 5,060 **Pixels (H x V):**

2.5 x 2.5 **Pixel Size, H x V (µm):**

12.65 x 12.65 **Sensing Area, H x V (mm):**

E2525A **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Global **Shutter Type:**

8/10/12 Bit **Pixel Depth:**

hardware trigger & freely programmable **Exposure Time:**

68 dB **Dynamic Range (dB):**

GigE Vision 2.0, GenICam **Machine Vision Standard:**

## Electrical

3.1 W **Power Consumption (W):**

## Hardware & Interface Connectivity

GigE **Interface:**

GigE, RJ45 with Screw Locks **Connector:**

PoE or 12-24 VDC **Power Supply:**

1 opto-coupled input line, 2 general purpose I/O (GPIO) lines **GPIOs:**

Hardware Trigger (GPIO), Software Trigger, or Free Run **Synchronization:**

Back Panel **Interface Port Orientation:**

M8 6-pin **GPIO Connector Type:**

## Threading & Mounting

C-Mount **Mount:**

1/4-20 with Tripod Mount Adapter #16-641 **Mounting Threads:**

## Environmental & Durability Factors

-10 °C - 60 °C **Operating Temperature (°C):**


## Regulatory Compliance

## Product Details


- SONY Pregius S Sensors Available with up to 24MP
- Proven Compact Housing (29 x 29mm)
- Powerful Computer Vision Feature Set with Optional Beyond Features
- [Basler ace GigE Cameras](#) Also Available

Basler ace2 GigE/5GigE Cameras are available in two versions that provide optimized hardware design, proven compact and robust housing, and state of the art CMOS sensor technology with excellent image quality from Sony's 2nd-Gen Pregius, 3rd-Gen STARVIS, or the latest 4th-Gen Pregius S sensors. These second-generation Ace cameras include all of the components of the first-generation Ace cameras along with integrated features such as a status LED, removable IR cut filter, and robust M8 connector. The Basler ace2 GigE/5GigE Camera Basic version offers excellent price to performance ratio with powerful Computer Vision feature set, while the Pro version unlocks unique advanced Beyond features such as Pixel Beyond and Compression Beyond for maximum performance to meet with demanding application requirements. These cameras include the industry proven Basler Pylon SDK Software and Driver and conform to GenICam (GigE Vision 2.0) standards, making them a fast and cost-effective solution to software integration. Basler ace2 Cameras are available in both GigE, 5GigE and USB3.0 interfaces and are ideal for a wide range of applications such as factory automation and industrial robotics.


## Technical Information




IMX676 Sensor QE Curve



IMX900 Sensor QE Curve



GMAX2505 Sensor QE Curve



IMX546 Sensor QE Curve



IMX545 Sensor QE Curve



GMAX2509 Sensor QE Curve



GMAX2518 Sensor QE Curve



IMX547 Sensor QE Curve



E2525A Sensor QE Curve