

# FLIR T198534 Power Supply for EX Series USB Micro



Stock #75-083 **NEW** 2 In Stock

1 **£48<sup>.44</sup>**

**ADD TO CART**

Volume Pricing	
Qty	£48.44
1+	each
Need More?	<a href="#">Request Quote</a>

Prices shown are exclusive of VAT/local taxes

Product Downloads

- Spec Sheets:pdf
- [Download All](#)

## General

**Model Number:** Ex Series

## Regulatory Compliance

**Certificate of Conformance:** [View](#)

## Product Details

- Professional-Grade thermal Imagers for Industrial Applications
- Rugged, Handheld Design for Field Use
- Wide Temperature Ranges up to 550°C (1022°F)
- Wi-Fi for Fast Image Transfer and Reporting

The FLIR Ex Series delivers professional-grade thermal imaging in a rugged, handheld design built for demanding field environments. Offering industry-leading infrared resolution and wide temperature measurement ranges up to 550°C (1022°F), the E5 Pro, E6 Pro, and E8 Pro models are ideal for maintenance, building inspections, electrical diagnostics, HVAC servicing, and industrial troubleshooting. The E5 Pro (160 × 120 resolution) provides reliable thermal imaging for general inspections, the E6 Pro (240 × 180 resolution) offers enhanced resolution for identifying smaller temperature variations, and the E8 Pro (320 × 240 resolution) delivers the highest clarity and thermal sensitivity for advanced diagnostics. Built-in Wi-Fi connectivity allows for fast image transfer, reporting, and data sharing directly from the field, streamlining workflows and improving efficiency. With precision thermal sensitivity down to 0.04°C on the E8 Pro, users can detect subtle heat patterns and prevent equipment failures before they occur. The Ex Series combines FLIR's trusted infrared technology with durability and portability, making it a top choice for professional thermal imaging applications.

Model	E5 Pro	E6 Pro	E8 Pro
Resolution	160 × 120 (19,200 pixels)	240 × 180 pixels (43,200 pixels)	160 × 120 (19,200 pixels)
Temp Range	-20°C to 400°C (-4°F to 752°F)	-20°C to 550°C (-4°F to 1022°F)	-20°C to 550°C (-4°F to 1022°F)
Thermal sensitivity	<0.06°C	<0.05°C	<0.04°C

**Accuracy:** ±2°C (±3.6°F) or ±2% of reading, for ambient temperature 10°C to 35°C (50°F to 95°F) and object temperature above 0°C (32°F)

# Accessories

**Note:** Compatible accessories for individual stock numbers may vary. If unsure about which accessories work with your products, please contact us [here](#).

	Title	Compare	Stock Number	Price	Buy
<a href="#">MORE+</a>	FLIR T198528 Hard Transport Carrying Case for Ex series		#75-077 <b>NEW</b>	<b>£220.15</b> <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/>
<a href="#">MORE+</a>	FLIR T300772ACC External Battery Charger for Ex Series		#75-080 <b>NEW</b>	<b>£139.40</b> <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/>
<a href="#">MORE+</a>	FLIR T198532 Micro USB Car Charger for EX Series		#75-081 <b>NEW</b>	<b>£66.29</b> <a href="#">Request Quote</a>	2 In Stock <input type="text" value="1"/>
<a href="#">MORE+</a>	FLIR T198533 USB Cable for EX Series		#75-082 <b>NEW</b>	<b>£55.24</b> <a href="#">Request Quote</a>	2 In Stock <input type="text" value="1"/>
<a href="#">MORE+</a>	FLIR T198534 Power Supply for EX Series USB Micro		#75-083 <b>NEW</b>	<b>£48.44</b> <a href="#">Request Quote</a>	2 In Stock <input type="text" value="1"/>
<a href="#">MORE+</a>	FLIR T199362ACC Replacement Battery for the Ex Series		#75-084 <b>NEW</b>	<b>£203.15</b> <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/>
<a href="#">MORE+</a>	FLIR T911093 Tool Belt for the Ex Series		#75-087 <b>NEW</b>	<b>£55.24</b> <a href="#">Request Quote</a>	2 In Stock <input type="text" value="1"/>
<a href="#">MORE+</a>	FLIR T911689ACC Pouch Case for Ex Series		#75-088 <b>NEW</b>	<b>£84.14</b> <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/>

## Related Products



Lightpath® Thermal Imaging Assemblies



Athermal Imaging Lenses



Temperature Sensitive Liquid Crystal Sheets