

Gold Coated Optotune Fine Steering Mirror

See More by [Optotune](#)



Gold Coated Optotune Fine Steering Mirror



Stock **#23-715** [CONTACT US](#)

-

1

+

£765⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£765.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

Physical & Mechanical Properties

50.8 x 50.8 x 12

Dimensions (mm):

53	Weight (g):
20 x20	Mirror Size (mm) :
Optical Properties	
2λ @ 549nm	Surface Flatness (P-V):
Protected Gold (800-2000nm)	Coating:
0.4 (in x and y)	Scan Angle (°):
R _{avg} >95% @ 800 - 2000nm (0-45°)	Coating Specification:
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Milliradian (mrad) Beam Steering Range With μrad Resolution
- Metallic or Dielectric Coatings for Low to High Power Lasers
- Ideal for Laser Wobbling Applications

Optotune Fine Steering Mirrors are designed for laser systems requiring precise, fast tilting with high angular resolution. These mirrors have a large clear aperture to create two-dimensional beam patterns for a variety of laser wobbling applications, including laser cavity alignment, Lissajous scanning, and laser soldering. Each device has a temperature sensor and EEPROM containing calibration data for precise open-loop control. Optotune Fine Steering Mirrors are available with metallic or dielectric coatings for use with low to high power laser beams and are easily driven using the Optotune ICC-4C-2000 controller.