

IDS GV-5200FA-M-GL, GigE, 1.1" Monochrome Camera

The image shows the IDS logo on the left, consisting of the letters 'IDS' in a bold, sans-serif font, followed by three vertical bars of increasing height. To the right of the logo is a close-up of a camera lens, showing the glass element and the surrounding metal housing. The lens is reflecting a bright blue light. The entire image is set against a dark, reflective background.



⊖ 1 ⊕ £1,984^{.00}

Volume Pricing	
Qty 1+	£1,984.00 each
Need More?	Request Quote

Product Downloads

Spectrum:

Monochrome Camera

Type:

GV-5200FA-M-GL

IDS Imaging Development Systems	Manufacturer:
uEye+ FA	Camera Series:
Physical & Mechanical Properties	
41 x 53 x 42.7 (excludes connectors and lens mount)	Dimensions (mm):
173	Weight (g):
Full	Housing:
Sensor	
128MB	Image Buffer:
1.1"	Sensor Format:
12.29	Resolution (Megapixels):
10.00	Frame Rate (fps):
4,104 x 3,006	Pixels (H x V):
3.45 x 3.45	Pixel Size, H x V (µm):
14.158 x 10.37	Sensing Area, H x V (mm):
Sony IMX304	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
12 bit	Pixel Depth:
0.046ms - 2000ms	Exposure Time:
70.00	Dynamic Range (dB):
GigE Vision	Machine Vision Standard:
Electrical	
1.7 - 3.1	Power Consumption (W):
Hardware & Interface Connectivity	
GigE (PoE)	Interface:
GigE M12, screwable	Connector:
Power over Ethernet (PoE) or 12 - 24VDC via GPIO with #19-692	Power Supply:
2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Voltage Output, 1 Ground	GPIOs:
Hardware Trigger (GPIO); Software Trigger	Synchronization:
Back Panel	Interface Port Orientation:
8-pin Binder connector (Binder series 712: 09-0427-020-08)	GPIO Connector Type:
Threading & Mounting	
C-Mount	Mount:
¼-20 with Tripod Mount Adapter #19-694	Mounting Threads:
Environmental & Durability Factors	
0 to +55	Operating Temperature (°C):
	Storage Temperature (°C):

Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- Designed for Harsh Environments
- Robust IP65/67 Housing for Dust and Washdown Protection
- Compatible with [TECHSPEC® Cw Series Lenses](#)
- IP65/67 Rated Accessories and Illumination Also Available

IDS Imaging uEye+ FA IP65/67 PoE Cameras feature robust IP65/67 rated housings to withstand harsh industrial environments, providing protection against dirt, dust, and water. These cameras provide plug-and-play functionality and require no additional enclosures when paired with [TECHSPEC® Cw Series Lenses](#). Featuring IP65/67 rated accessories, these cameras utilize IDS Imaging's latest Peak SDK platform that supports GenICam and GigE Vision standards, simplifying system integration and software development. IDS Imaging uEye+ FA IP65/67 PoE Cameras are ideal for a wide variety of demanding applications requiring washdown and dust resistance including factory automation, medical technology, and machine vision.