

[See all 15 Products in Family](#)

Coherent® EnergyMax 1110747 | 50μJ-100mJ, DB25

See More by [Coherent®](#)



Coherent® EnergyMax Laser Energy Sensors

Stock **#12-387** [CONTACT US](#)

-

 1

+

£1,608^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£1,608.00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Model Number:	
J-25MT-10KHZ Coherent Part Number: 1110747	
Type:	
Meter required	
Linearity (%):	
±3	
Calibration Uncertainty (%):	
±2	

<2	Noise Equivalent Energy (μJ):
	Compatible Meters:
#35-203	
Maximum Incident Energy Density: 500mJ/cm ² (10ns, 1064nm)	
50μJ - 100mJ	Energy Range:
Preferred Meter:	
#88-412	
Physical & Mechanical Properties	
25	Active Area Diameter (mm):
Optical Properties	
1064	Calibration Wavelength (nm):
1.7	Maximum Pulse Width (μs):
Wavelength Range (nm):	
190 - 2100	
Sensor	
Pyroelectric	Type of Sensor:
Electrical	
10000	Maximum Repetition Rate (pps):
10	Maximum Incident Beam Power (W):
Hardware & Interface Connectivity	
DB25	Connector:
2.5	Length of Cable (m):
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
Certificate of Conformance:	
View	

Product Details

- ISO 17025 Certified
- Embedded Spectral Compensation Characteristics
- Automatic Temperature Compensation

Coherent® EnergyMax Laser Energy Sensors are designed for a variety of demanding laser measurement applications. These energy sensors, available in meter or meterless USB configurations, incorporate a diffuse coating to minimize specular reflection and feature large active areas. The J-50MB-YAG combines the MaxBlack coating with a diffuser for use with high energy lasers of up to 3J. Coherent® EnergyMax Laser Energy Sensors utilize onboard sensors to automate temperature compensation for improved measurement accuracy.