See all 4 Products in Family

Dual Axis Linear Scale Micrometer

Stock **#58-608** **4 In Stock**

- 1 + **£532**.00

ADD TO CART

Volume Pricing	
Qty 1-4	**£532.00** each
Qty 5+	**£505.84** each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

NIST Certification:

No

Physical & Mechanical Properties

Scale Divisions:

Metric: 25µm
English: 1 mil (0.001")

Dimensions (mm):

25.4 x 76.2

Thickness (mm):
1.50 ±0.100

Dimensional Tolerance (mm):
±0.100

Optical Properties

Substrate:
Chrome on Glass

Surface Quality:
60-40

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 235:
Compliant

Product Details

- Dual Axis Design
- English and Metric Scales
- NIST Certified Version Available

Our Linear Scale Stage Micrometer is designed to accurately calibrate machine vision systems simultaneously in the X- and Y- axes. This allows calibration without rotation, and without compensation for camera aspect ratios. Micrometer features two scales – a metric scale featuring 25µm divisions, and an English scale featuring 1 mil (0.001") divisions. Target is chrome on glass or chrome on opal.

Technical Information



;