

TECHSPEC® Infinite Conjugate, UV Coated, 15X/0.28NA ReflX Objective



Stock **#58-417** 3-4 DAYS

- 1 + **£1,894.65**

ADD TO CART

Qty 1+
£1,894.65
Qty 2+
£1,673.65
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Entrance Pupil Position (mm):
7.4 (Diameter)

Horizontal Field of View, 1/2" Sensor:
0.43mm

Horizontal Field of View, 2/3" Sensor:
0.59mm

Focal Length FL (mm):

13.30
Coating: Enhanced Aluminum (200-11000nm)
Magnification: 15X
Numerical Aperture NA: 0.28
Mounting Threads: RMS
Type: Microscope Objective
Obscuration (%) : 27.00
Transmitted Wavefront, RMS: λ/10
Diameter of Small Mirror (mm): 8.8
Working Distance (mm): 23.75
Aperture Diameter (mm): 8.5
Note: Requires a 200mm secondary tube lens
Coating Specification: R _{avg} >85% @ 200 - 700nm (typical) R _{avg} >76% @ 700 - 1750nm (typical) R _{avg} >96% @ 1750 - 11000nm (typical)
Wavelength Range (nm): 200 - 11000
Style: Infinity Corrected
Manufacturer: Edmund Optics®

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View