


[See all 20 Products in Family](#)

## InGaAs Variable Gain Photoreceiver, 900-1700nm



Stock #90-630 **NEW** 1 In Stock

- 1 + £3,448.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	£3,448.00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Remote Control:  
Yes

Note:  
Includes:  
LEMO® 3-pin connector  
Datasheet

### Physical & Mechanical Properties

Weight (g):  
320

Case Size: 170 x 60 x 45

Dimensions (mm):

## Optical Properties

900 - 1700 nm

Spectral Range:

## Sensor

InGaAs PIN

Detector Type:

## Electrical

**Transimpedance Gain ( $\Omega$ ):**  
Low Noise:  $1 \times 10^3$  -  $1 \times 10^9$ (adjustable in decade steps)  
High Speed:  $1 \times 10^4$  -  $1 \times 10^9$ (adjustable in decade steps)

**Noise Equivalent Power NEP ( $W/Hz^{1/2}$ ):**  
 $4.7 \times 10^{-14}$  -  $1.8 \times 10^{-10}$

200 MHz max

Bandwidth (-3 db):

## Hardware & Interface Connectivity

**Power Requirement:**  
 $\pm 15$  V,  $+150$  mA -  $100$  mA,  $\pm 200$  mA

**Power Supply:**  
Power Supply Required and Sold Separately.  
USA: [#59-180](#)  
Europe: [#59-180](#)  
Japan: Not Available  
Korea: Not Available  
China: [#59-180](#)

## Environmental & Durability Factors

0 to +60

Operating Temperature ( $^{\circ}C$ ):

## Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

## Product Details

- Ultra-Wide Adjustable Transimpedance Gain from  $10^2$  to  $10^{11}$  V/W
- Exceptional Low-Noise, High-Sensitivity Single-Beam Detection
- Optimized for Absolute Optical Power Measurements
- Designed for Direct, Alignment-Free Integration

Variable Gain Photoreceivers feature an ultra-wide adjustable transimpedance gain from  $10^2$  to  $10^{11}$  V/W, enabling precise measurement of optical signals across a broad power range. Engineered for ultra-low noise performance, these photoreceivers achieve noise equivalent power (NEP) as low as  $6$  fW/√Hz, ensuring accurate detection of extremely weak optical signals. Designed for single-beam detection, they provide maximum sensitivity and dynamic range, allowing for simple, alignment-free integration into optical systems. Variable Gain Photoreceivers are ideal for applications such as photonics research, optical communication testing, and precision low-light measurements.

**Note:** Power supply sold separately. Please see specifications for more details.