

## Laminated Wratten ND Filter 2.0 OD 25mm Dia



Stock #29-317 **20+ In Stock**

1  £80<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-10	£80.00 each
Qty 11-25	£64.80 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Neutral Density Filter **Type:**

Supplied with protective film on both sides **Note:**

#### Physical & Mechanical Properties

25.00 +/- 0.25 **Diameter (mm):**

## Optical Properties

**Optical Density OD (Average):**

2

**Substrate:**

Wratten 2 Filter, One-Side Laminated onto PMMA

**Coating:**

Uncoated

**Blocking Wavelength Range (nm):**

400-700

## Regulatory Compliance

**Certificate of Conformance:**

[View](#)

## Product Details

- One-Side Laminated for Stability
- Available in 25mm and 48mm Sizes
- Kodak Filter No. 96
- Lightweight Alternative to Traditional Glass ND Filters

PMMA-Laminated Wratten ND Filters are ideal for light attenuation in image-forming optical systems to reduce light intensity across the visible spectrum without altering the spectral profile. The laminated design offers additional stability and durability compared to traditional polyester/gelatin filters while remaining a lightweight alternative to traditional glass ND filters. These ND filters are available in 25mm or 48mm diameters and a thickness of 0.6mm. PMMA-Laminated Wratten ND Filters are uncoated and feature a blocking wavelength of 400 - 700nm with OD options of 0.1, 0.3, 0.5, 1.0, 2.0, and 3.0.