

[See all 15 Products in Family](#)

Laser Safety Window LS05 RB2 100 x 200mm



Laser Safety Windows

Stock **#29-376** **1 In Stock**

⊖ 1 ⊕ £102⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£102.40 each
Qty 6-10	£92.16 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

EN 207/208 Ratings:

D LB6 and R LB4 @ 180-315nm
 DR LB4 @ 315-400nm
 DIR LB3 @ 615-660nm
 DIR LB4 @ 660-665nm
 D LB4 and IR LB5 @ 665-715nm
 IR LB7 @ 694nm

Filter Material:

Polymer

LS05

Filter:

Physical & Mechanical Properties

100 x 200 **Dimensions (mm):**

3.00 **Thickness (mm):**

Optical Properties

Optical Density OD (Average):
>6 @ 190 - 400nm
>3 @ 615 - 720nm
>4 @ 651 - 670nm
>5 @ 671 - 715nm
>6 @ 680 - 710nm
>7 @ 690 - 700nm

Aqua **Color:**

35 **Visible Light Transmission VLT (%):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- CE Certified Laser Radiation Protection
- Available for UV, VIS, and NIR Wavelengths
- 200mm x 100mm Size Ideal for Small Enclosures
- 304.8mm x 304.8mm Sizes Also Available

Laser Safety Windows feature high optical density in a specified wavelength range across the UV, VIS, and NIR spectra. Made from acrylic and polycarbonate, these laser safety windows are CE certified to protect against laser radiation. These windows are available in 200 x 100mm for easy integration into small equipment doors, windows, and enclosures. 304.8 x 304.8mm sizes are also available. Laser Safety Windows are ideal for blocking laser radiation while providing safe viewing of laser environments in materials processing, manufacturing, and laboratory applications featuring Nd:YAG, CO₂, fiber, and other laser sources.

Warning: Because of the potential for eye damage, the degree of protection required in each circumstance should be determined by the Laser Safety Officer, the industrial hygienist, or the individual responsible for the safety program.