

## Hydrogen Cyanide Fiber-Coupled Gas Cell, 16.5 cm Path Length, FC/APC



Stock #72-200 [CONTACT US](#)

- 1 + £820.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-4	£820.00 each
Qty 5-9	£738.00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

16.5 Path Length (cm):

FC/APC Fiber Connector Type:

### General

Hydrogen Cyanide (H<sup>13</sup> C<sup>14</sup> N) Type:

HCN-13-H(16.5)-25-FCAPC Model Number:

## Optical Properties

Wavelength Range (nm):

1525 - 1565

Transmission (%):

>50

## Environmental & Durability Factors

Operating Temperature (°C):

0 to +70

## Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- Hydrogen Cyanide and Acetylene Gasses Available for Wavelength Coverage of 1510 to 1565nm
- FC and SC Fiber Connection Options with a Variety of Path Lengths Available
- NIST Traceable Reference Cells

Wavelength References Fiber-Coupled Gas Cells are FC/APC, SC/APC, FC/PC, or SC/PC connected fiber coupled, gas filled precision filters whose absorption wavelengths depend on specific molecular energy level transitions that may be used as wavelength standards. Hermetically sealed to maintain >10 year lifetime, these gas cells feature metal housings, wedged windows, and coated optics for minimum interference artifacts and can be easily integrated into existing benchtop systems. Wavelength References Fiber-Coupled Reference Cells are available with a variety of path lengths and pressures which meet the requirements of NIST Standard Reference Material® (SRMs) 2517a, 2519, or 2519a. Short path lengths are recommended for measuring gasses at high concentration while longer path lengths enable more sensitive measurements. These reference cells are ideal for spectroscopy, wavelength/frequency locking, laser calibration, and optical gas sensing systems. Hydrogen Cyanide ( $H^{13}C^{14}N$ ) has been identified by national standards bodies as the primary wavelength reference in the C-band (1530 – 1565nm) while Acetylene ( $^{12}C_2H_2$ ) is recognized as a primary wavelength reference in the 1510 to 1540nm band.