

LightPath 354115 | 9.2mm Dia., 0.54 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#16-691** **20+ In Stock**

-

1

+

£71^{.20}

ADD TO CART

Volume Pricing	
Qty 1-10	£71.20 each
Qty 11-49	£64.00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Compatible Window:	
Thickness: 0.25 (t) (mm) Material: BK7	
Lightpath Lens Code:	
354115	
Type:	
Aspheric Lens	
Typical Applications:	

Collimate or Focus Laser Light

Physical & Mechanical Properties

9.20 ±0.015	Diameter (mm):
7	Clear Aperture CA (mm):
2.15	Edge Thickness ET (mm):
4.08 ±0.02	Center Thickness CT (mm):
Protective as needed	Bevel:

Optical Properties

6.75 @ 633nm	Effective Focal Length EFL (mm):
0.54	Numerical Aperture NA:
D-ZK3	Substrate: □
±1	Focal Length Tolerance (%):
633	Aspheric Design Wavelength (nm):
BBAR (350-700nm)	Coating:
R _{avg} ≤0.5% @ 350 - 700nm	Coating Specification:
60-40	Surface Quality:
0.93	f/#:
350 - 700	Wavelength Range (nm):
4.3	Working Distance (mm):
Infinite	Conjugate Distance:
<0.087	Transmitted Wavefront Error (λ, RMS):

Environmental & Durability Factors

≤200	Operating Temperature (°C):
------	-----------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.


LASER OPTICS

MADE BY EDMUND OPTICS®



LEARN MORE

Technical Information



;