

Glan-Taylor Polarizer 200 - 350nm, 12.7mm



Glan-Taylor Polarizer

Stock **#89-550** **1 In Stock**

-

1

+

£1,196⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£1,196.00 each
Qty 6+	£1,116.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Linear Polarizer	Type:
Physical & Mechanical Properties	
12.7	Clear Aperture CA (mm):
25.40	Diameter (mm):

21.00	Length (mm):
Crystalline Glan-Taylor Polarizer	Construction:
Optical Properties	
Single Layer MgF ₂	Coating:
<5 x 10 ⁻⁶	Extinction Ratio:
α-BBO	Substrate: ☐
20-10	Surface Quality:
λ/2 @ 632.8nm	Transmitted Wavefront, P-V:
<3	Beam Deviation (arcmin):
λ/4 @ 632.8 nm	Transmitted Wavefront Distortion (RMS):
200 - 350	Wavelength Range (nm):
2 J/cm ² @ 1064nm, 10ns, 10Hz	Damage Threshold, By Design: ☐

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:


Product Details

- High Extinction Ratios up to 200 000:1
- High Laser Damage Thresholds up to 5 J/cm² @ 1064nm

Glan-Type Polarizers are mounted, polarizing prisms used in applications that require broad spectral ranges, high extinction ratios, or high polarization purities. Glan-Taylor Polarizers are medium-power, air-spaced UV to NIR polarizers that transmit the extraordinary beam. The ordinary beam is then reflected and absorbed by black glass plates that have been cemented to the prism. Glan-Laser Polarizers are similar to Glan-Taylor, but are designed for higher power applications and appropriate for use in Q-switched laser cavities. Glan-Laser Polarizers utilize an advanced polishing technique for minimizing surface scatter and feature two escape windows for passing the high power rejected light. Glan-Thompson Polarizers are low power polarizers that are ideal for UV, visible, or NIR applications, feature a cemented design, and transmit the extraordinary beam while absorbing the reflected ordinary beam.

LASER OPTICS


MADE BY EDMUND OPTICS®




LEARN MORE

Technical Information

Glan-Taylor Polarizers



Glan-Laser Polarizers



Glan-Thompson Polarizers