


Glan-Thompson Polarizer 350 - 2200nm, 10mm



Glan-Thompson Polarizer

Stock **#89-545** **1 In Stock**

-

1

+

£748⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£748.00 each
Qty 6+	£708.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Linear Polarizer

Type:

Physical & Mechanical Properties

10.0

Clear Aperture CA (mm):

25.40

Diameter (mm):

33.00	Length (mm):
Crystalline Glan-Thompson Polarizer	Construction:
Optical Properties	
Single Layer MgF ₂	Coating:
<5 x 10 ⁻⁵	Extinction Ratio:
Calcite	Substrate: ☐
20-10	Surface Quality:
λ/2 @ 632.8nm	Transmitted Wavefront, P-V:
<3	Beam Deviation (arcmin):
λ/4 @ 632.8 nm	Transmitted Wavefront Distortion (RMS):
350 - 2200	Wavelength Range (nm):
1 J/cm ² @ 1064nm, 10ns, 10Hz	Damage Threshold, By Design: ☐

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details


- High Extinction Ratios up to 200 000:1
- High Laser Damage Thresholds up to 5 J/cm² @ 1064nm

Glan-Type Polarizers are mounted, polarizing prisms used in applications that require broad spectral ranges, high extinction ratios, or high polarization purities. Glan-Taylor Polarizers are medium-power, air-spaced UV to NIR polarizers that transmit the extraordinary beam. The ordinary beam is then reflected and absorbed by black glass plates that have been cemented to the prism. Glan-Laser Polarizers are similar to Glan-Taylor, but are designed for higher power applications and appropriate for use in Q-switched laser cavities. Glan-Laser Polarizers utilize an advanced polishing technique for minimizing surface scatter and feature two escape windows for passing the high power rejected light. Glan-Thompson Polarizers are low power polarizers that are ideal for UV, visible, or NIR applications, feature a cemented design, and transmit the extraordinary beam while absorbing the reflected ordinary beam.


LASER OPTICS

MADE BY EDMUND OPTICS®


Technical Information



Glan-Taylor Polarizers



Glan-Laser Polarizers



Glan-Thompson Polarizers