

LightPath 353215 | 4mm Dia., 0.30 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#71-004** 20+ In Stock

-

1

+

£95⁴³

ADD TO CART

Volume Pricing	
Qty 1-10	£95.43 each
Qty 11-49	£84.05 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

355215Lightpath Lens Code:

Aspheric Lens	Type:
Collimate or Focus Laser Light	Typical Applications:
Physical & Mechanical Properties	
4.00 ±0.015	Diameter (mm):
3.5	Clear Aperture CA (mm):
2.284	Edge Thickness ET (mm):
2.80 +/-0.025	Center Thickness CT (mm):
Protective as needed	Bevel:
Optical Properties	
6.20 @520nm	Effective Focal Length EFL (mm):
0.30	Numerical Aperture NA:
H-FK61M	Substrate: □
±1	Focal Length Tolerance (%):
520	Aspheric Design Wavelength (nm):
BBAR (350-700nm)	Coating:
R _{avg} ≤0.5% @ 350 - 700nm	Coating Specification:
40-20	Surface Quality:
1.55	f/#:
350 - 700	Wavelength Range (nm):
4.33	Working Distance (mm):
Infinite	Conjugate Distance:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

PRODUCT DETAILS

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



TECHNICAL INFORMATION

