

IDS GV-5240FA-NIR-GL, GigE, 1/1.8" Monochrome Camera NIR

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ FAIP65/67 PoE Cameras (Front)



Stock #26-297 **5 In Stock**

⊖ 1 ⊕ £760⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | £760.00 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

Spectrum:
NIR

General

Type:
Mono NIR

Model Number:
GV-5240FA-NIR-GL

IDS Imaging Development Systems **Manufacturer:**

uEye+ FA **Camera Series:**

Physical & Mechanical Properties

41 x 53 x 42.7 (excludes connectors and lens mount) **Dimensions (mm):**

173 **Weight (g):**

Full **Housing:**

Sensor

128MB **Image Buffer:**

1/1.8" **Sensor Format:**

1.31 **Resolution (Megapixels):**

59.00 **Frame Rate (fps):**

1,280 x 1,024 **Pixels (H x V):**

5.30 x 5.30 **Pixel Size, H x V (µm):**

6.784 x 5.427 **Sensing Area, H x V (mm):**

e2v EV76C661 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Rolling / Global / Global Start **Shutter Type:**

10 bit **Pixel Depth:**

0.009ms - 169ms **Exposure Time:**

63.00 **Dynamic Range (dB):**

GigE Vision **Machine Vision Standard:**

Electrical

1.7 - 2.2 **Power Consumption (W):**

Hardware & Interface Connectivity

GigE (PoE) **Interface:**

GigE M12, screwable **Connector:**

Power over Ethernet (PoE) or 12 - 24VDC via GPIO with [#19-692](#) **Power Supply:**

2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Voltage Output, 1 Ground **GPIOs:**

Hardware Trigger (GPIO); Software Trigger **Synchronization:**

Back Panel **Interface Port Orientation:**

8-pin Binder connector (Binder series 712: 09-0427-020-08) **GPIO Connector Type:**

Threading & Mounting

C-Mount **Mount:**

¼-20 with Tripod Mount Adapter [#19-694](#) **Mounting Threads:**

Environmental & Durability Factors

0 to +55 **Operating Temperature (°C):**

-20 to +60

Storage Temperature (°C):

Regulatory Compliance

[Exempt](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Contains SVHC\(s\)](#)

REACH 241:

Product Details

- Designed for Harsh Environments
- Robust IP65/67 Housing for Dust and Washdown Protection
- Compatible with [TECHSPEC® Cw Series Lenses](#)
- IP65/67 Rated Accessories and Illumination Also Available

IDS Imaging uEye+ FA IP65/67 PoE Cameras feature robust IP65/67 rated housings to withstand harsh industrial environments, providing protection against dirt, dust, and water. These cameras provide plug-and-play functionality and require no additional enclosures when paired with [TECHSPEC® Cw Series Lenses](#). Featuring IP65/67 rated accessories, these cameras utilize IDS Imaging's latest Peak SDK platform that supports GenICam and GigE Vision standards, simplifying system integration and software development. IDS Imaging uEye+ FA IP65/67 PoE Cameras are ideal for a wide variety of demanding applications requiring washdown and dust resistance including factory automation, medical technology, and machine vision.
