

## M25.5 x 0.5 Mounted Linear Glass Polarizing Filter



Mounted Linear Glass Polarizing Filters

Stock #46-575 **20+ In Stock**

⊖ 1 ⊕ £43<sup>20</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	£43.20 each
Qty 10+	£39.00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Mounted Imaging Filter **Type:**

### Physical & Mechanical Properties

22.5 **Clear Aperture CA (mm):**

27.50 **Diameter (mm):**

Dichroic **Construction:**

## Optical Properties

Uncoated **Coating:**

Approx. 19:1 at 400nm  
Approx. 200:1 at 500nm  
≥2700:1 at 550-650nm  
Approx. 600:1 at 700nm **Extinction Ratio:**

Float Glass **Substrate:** □

95% Efficiency **Polarization:**

Single: 30  
Crossed: 0.15 **Transmission (%):**

400 - 700 **Wavelength Range (nm):**

## Threading & Mounting

M25.5 x 0.50 **Filter Thread:**

8 **Mount Thickness (mm):**

10 **Mount Thickness Including Threads (mm):**

## Environmental & Durability Factors

-15 to +70 **Operating Temperature (°C):**

## Regulatory Compliance

[Compliant](#) **Reach 174:**

[View](#) **Certificate of Conformance:**

## Product Details

- Stackable, Rotating Mount for Easy Integration into Imaging Systems
- Eliminate Hot Spots and Reduce Glare
- 95% Polarization Efficiency
- Also Available [Unmounted](#)

Mounted Linear Glass Polarizing Filters feature a rotatable threaded mount available in a wide range of standard thread sizes. Linear polarizing filters will transmit a single axis of polarization and can be used to reduce glare and hot spots in imaging systems. Two polarizing filters can be stacked to achieve a variable density effect. Thickness includes a 2mm male thread. Mounted Linear Glass Polarizing Filters have 95% polarization efficiency. The filters are also available [unmounted](#).

## Technical Information

