


[See all 4 Products in Family](#)

Micro Line and Dot Standard Stage Micrometer on Opal Glass



Stock #58-762 [CONTACT US](#)

⊖ 1 ⊕ £1,012⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	£1,012.00 each
Qty 5+	£962.24 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

No **NST Certification:**

Physical & Mechanical Properties

Scale Divisions:
2µm, 3µm, 4µm, 5µm, 6µm, 7µm, 8µm, 9µm, 10µm,
25µm, 50µm, 75µm, 100µm

Dimensions (mm):
25.4 x 76.2

1.50 ±0.100 **Thickness (mm):**

±0.100 **Dimensional Tolerance (mm):**

Optical Properties

Chrome on Opal Glass **Substrate:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 235:**

Product Details

- New Opal Version Available
- Calibrate Pixel Dithering
- Lines and Dot Range from 2µm to 100µm

The Micro Line and Dot Standard is designed to calibrate imaging devices performing critical measurements. The pattern features known dot and line sizes of 2µm, 3µm, 4µm, 5µm, 6µm, 7µm, 8µm, 9µm, 10µm, 25µm, 50µm, 75µm, 100µm. Calibrating with this target can limit the effects of pixel dithering in image processing algorithms. Target is chrome on glass or chrome on opal.

;