

TECHSPEC[®] Multi-Element Outer Tube Joining Ring



Multi-Element Outer Tube Joining Ring



Stock #11-179 **10 In Stock**

-

1

+

£46⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-4	£46.40 each
Qty 5-9	£40.96 each
Qty 10+	£38.08 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Thread Adapter

Function:

Physical & Mechanical Properties

3.0	Extension Length (mm):
9.0	Total Length (mm):
24.5	Clear Aperture CA (mm):
Construction: Matte Black Anodized Aluminum (6061-T6)	
32.0	Outer Diameter (mm):
24.5	Inner Diameter (mm):

Threading & Mounting

M29 x0.75	Thread Type:
-----------	--------------

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 223:
View	Certificate of Conformance:

Product Details

- Continuous M29 x0.75 Internal Threading for Easy Lens Spacing
- Prevent Unwanted External and Stray Light from Entering the System
- Available in Multiple Lengths for Compact Systems
- Click [Here](#) to See How to Use the Multi-Element Tube System Components to Build an Optical System.

TECHSPEC® Multi-Element Outer Tubes provide a compact and contained system mounting solution. Available in five different lengths, these outer tubes allow for control of overall system length. The enclosed design and matte finish helps prevent unwanted external and stray light from entering the optical system. TECHSPEC® Multi-Element Outer Tubes feature M29 x0.75 internal threads along the entire optical axis, allowing for infinite optical spacing adjustment for both [TECHSPEC® Multi-Element Inner Single Optic Mounts](#) and [TECHSPEC® Multi-Element Inner Pair Optic Mounts](#). For harsh environment applications, the Multi-Element Retaining Ring Set ([#37-774](#)) is highly recommended to lock in lens spacing.

Note: The [TECHSPEC® Multi-Element Tube System Accessories](#) are recommended for easy system expansion or integration. The Multi-Element 2" Square Cage Interface Plate ([#11-213](#)) can be used to mount a Multi-Element Tube System Assembly to a [TECHSPEC Stainless Steel Mounting Post](#).