

[See all 14 Products in Family](#)

# LightPath 390017 | 3.5mm Dia., 0.72 NA, BBAR (3000-5000nm), Molded IR Aspheric Lens

See More by [Lightpath®](#)



Stock #83-718 **14 In Stock**

[Other Coating Options](#)

- 1 + £328<sup>00</sup>

**ADD TO CART**

#### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1-10   | £328.00 each                  |
| Qty 11-49  | £295.20 each                  |
| Need More? | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

#### Product Downloads

#### General

390017 **Lightpath Lens Code:**

Aspheric Lens **Type:**

#### Physical & Mechanical Properties

**Diameter (mm):**

|                      |                                  |
|----------------------|----------------------------------|
| 3.50 ±0.015          |                                  |
| 2.60                 | <b>Clear Aperture CA (mm):</b>   |
| 0.72                 | <b>Edge Thickness ET (mm):</b>   |
| 1.10                 | <b>Center Thickness CT (mm):</b> |
| Protective as needed | <b>Bevel:</b>                    |

## Optical Properties

|   |  |
|---|--|
| 1.50 @2300nm  | <b>Effective Focal Length EFL (mm):</b>            |
| 0.72  | <b>Numerical Aperture NA:</b>                      |
| Black Diamond™ BD-2 (Ge <sub>26</sub> Sb <sub>12</sub> Se <sub>60</sub> ) | <b>Substrate:</b> □                                |
| 2300  | <b>Aspheric Design Wavelength (nm):</b>            |
| BBAR (3000-5000nm)  | <b>Coating:</b>                                    |
| R <sub>avg</sub> <1.0% @ 3 - 5μm  | <b>Coating Specification:</b>                      |
| 80-50   | <b>Surface Quality:</b>                            |
| 0.69  | <b>f#:</b>   |
| 2.6023  | <b>Index of Refraction (n<sub>d</sub>) @ 10μm:</b> |
| 2.5843  | <b>Index of Refraction (n<sub>d</sub>) @ 14μm:</b> |
| 2.6210  | <b>Index of Refraction (n<sub>d</sub>) @ 4μm:</b>  |
| 2.6173  | <b>Index of Refraction (n<sub>d</sub>) @ 5μm:</b>  |
| 3000 - 5000   | <b>Wavelength Range (nm):</b>                      |
| 1.24  | <b>Working Distance (mm):</b>                      |
| Infinite  | <b>Conjugate Distance:</b>                         |
| 2300  | <b>Focal Length Specification Wavelength (nm):</b> |

## Material Properties

|  |   |
|--|---|
| 14.00  | <b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b> |
| 4.68   | <b>Density (g/cm<sup>3</sup>):</b>                                |
| 70 x 10 <sup>-6</sup> /°C from -40° to +80°C (5 - 14 μm) | <b>Thermo-optic coefficient dn/dT:</b>                            |
| 285.00   | <b>Transformation Temperature (°C):</b>                           |

## Regulatory Compliance

|                           |                                    |
|---------------------------|------------------------------------|
| <a href="#">Compliant</a> | <b>RoHS 2015:</b>                  |
| <a href="#">View</a>      | <b>Certificate of Conformance:</b> |
| <a href="#">Compliant</a> | <b>Reach 247:</b>                  |

## Product Details

- Wavelength Range of 1.8 - 12μm
- Variety of Coating Options
- Mounted and Unmounted Versions

LightPath® Mid-Wave and Long-Wave Infrared (IR) Aspheric Lenses feature a low-cost, molded design and offer several key benefits over Germanium substrate aspheres. With a dn/dT and CTE significantly less than that of Germanium, the lenses feature a smaller change in focal length as a function of temperature change. Featuring a higher operating temperature than Germanium (which suffers 20 – 30% transmission loss at 100°C), the lenses can be used in applications including collimators for QCL lasers and as components within thermal imaging assemblies. LightPath Mid-Wave and Long-Wave Infrared (IR) Aspheric Lenses have a wavelength range of 1.8 - 12μm. These lenses are available mounted or unmounted, in a variety of coating options.

# Technical Information

