

SWIR M37 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock **#28-823** **1 In Stock**

-

1

+

£296⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£296.00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Mounted Interference Longpass Filter	Type:
Physical & Mechanical Properties	
32.5	Clear Aperture CA (mm):
Mounted in Black Anodized Ring	Construction:
	Outer Diameter (mm):

Optical Properties	
	Blocking Wavelength Range (nm): 900-1270, 1340-1700
SWIR	Color:
	Center Wavelength CWL (nm): 1,300.00
	Full Width-Half Max FWHM (nm): 35.00
	Minimum Transmission (%): ≥90
Threading & Mounting	
	Filter Thread: M37 x0.75
	Mount Thickness (mm): 5.2
	Mount Thickness Including Threads (mm): 6.5
Regulatory Compliance	
View	Certificate of Conformance:
Compliant	Reach 242:

Product Details

- Optimized for Use with Popular LEDs
 - Multiple Mounting Sizes and Threads Available to Ease System Compatibility
 - ≥85% Transmission
 - [TECHSPEC® High Performance Mounted Machine Vision Filters](#) and [Mounted Color Filters](#) Also Available
- Mounted Machine Vision Filters are ideal for machine vision and industrial imaging applications. These mounted filters feature a wide range of common machine vision threads from M22 up to M105. Available in UV, VIS, and NIR wavelengths, these hard-coated filters provide exceptional transmission and out-of-band blocking. Mounted Machine Vision Filters are designed with a Gaussian transmission curve. When used with a broadband light source, Mounted Machine Vision Filters achieve the output profile of common LED wavelengths. While compatible with many types of imaging lenses, these filters are ideal for wide fields of view due to their low angular dependency.