

[See all 1 Products in Family](#)

IRis™ High Power Laser Detection Wand



Stock **#26-007** CLEARANCE **13 In Stock**

-

1

+

£728⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£728.00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Wand	Type:
Fiber Laser, Network Engineering	Typical Applications:

Physical & Mechanical Properties	
140 x 45	Dimensions (mm):

5.00	Thickness (mm):
35 x 35	Size of Active Area (mm):
Optical Properties	
IR	Wavelength:
40 MW/cm ² , 1540nm, 8.4ns pulses, 20 Hz	Damage Threshold, By Design: ☐
White	Emission Color:
1460 - 1600	Stimulation Range:
120 kW/cm ² , 1540nm, 8.4ns pulses, 20 Hz	Minimum Stimulation, Pulsed:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- 1460 – 1600nm Wavelength Range
- Lightweight and Portable
- Lanyard Clip for Hands Free Portability

The IRis™ High Power Laser Detection Wand is a laser detection wand designed to detect high powered infrared (IR) lasers commonly used in telecommunications datacenters. Designed with an infrared intelligent scintillator, this detection wand will fluoresce from laser inputs ranging from 1460 to 1600nm without producing false positives from lower power lasers. Featuring a glass active area and durable acrylic construction these detection wands are lightweight, portable, and robust making them suitable for indoor or outdoor use. The IRis™ High Power Laser Detection Wand is a passive device, requiring no external power and features a 35mm square anti-reflection coated active area, matte black finish, and lanyard. These detection wands are ideal for telecommunications and fiber optic work that require the validation and testing of high power IR lasers.