

Ocean Optics SR4 UV-VIS Spectrometer

See More by [Ocean Optics](#)



Stock **#90-020** NEW **2 In Stock**

-

1

+

£3,528⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£3,528.00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
OceanDirect & OceanView	Software:
3.8 ms – 2 s	Integration Time:
SR-4UW300-25	Model Number:
Includes manual QR code, software QR code, calibration reports for wavelength and linearity, 1 m USB cable	
Note:	

SMA905	Input Port Termination:
Ruled Diffraction Grating: 600 Grooves/mm, Blazed @ 300nm	Grating:
Cross Czerny Turner	Optical Bench:
Physical & Mechanical Properties	
25	Slit Width (µm):
0.275	Weight (kg):
88.1 x 63.5 x 31.45	Dimensions (mm):
Optical Properties	
1.65	Spectral Resolution (nm):
190 - 910	Wavelength Range (nm):
Sensor	
CCD	Type of Sensor:
Electrical	
Single Scan @ 10 ms: 250:1 Max per second with High Speed Averaging Mode: 3000:1	Signal to Noise S/N Ratio:
Hardware & Interface Connectivity	
USB, RS-232	Computer Interface:
Threading & Mounting	
(3) 4-40	Mounting Threads:
Environmental & Durability Factors	
0 to +55	Operating Temperature (°C):
-30 to +70	Storage Temperature (°C):
0.05 Pixel/°C	Thermal Stability:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

Product Details

- Compact Design and Powerful Performance
- Broad Wavelength Range Options Spanning 180 - 1040nm
- Three Models Available for a Diverse Range of Applications

Ocean Optics SR Versatile Spectrometers are available in S2, S4, and S6 models, each of which offers high performance and broad spectral coverage to suit a diverse set of applications. SR2 spectrometers are optimized for fast spectral acquisition and high signal-to-noise ratio (SNR), making them ideal for applications such as laser characterization, plasma monitoring, and absorbance concentration. The SR4 spectrometers present superior thermal wavelength stability, low-noise CCD detection, and consistent high signal-to-noise performance, perfect for plasma monitoring and reflection measurements. High-sensitivity SR6 models provide exceptional SNR and UV response, supporting applications such as UV absorbance, fluorescence, and plasma diagnostics. The Ocean Optics SR Versatile Spectrometers include the user-friendly OceanView software system to optimize spectrometer performance, ease system integration, and access data for analysis.