

[See all 15 Products in Family](#)

Coherent® EnergyMax 1191441 | 50μJ - 50mJ, USB

See More by [Coherent®](#)



Coherent® EnergyMax Laser Energy Sensors

Stock **#88-424** **2 In Stock**

-

1

+

£2,264^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£2,264.00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Model Number:	
J-25MB-LE Coherent Part Number: 1191441	
Type:	
Meterless	
Linearity (%):	
±3	
Calibration Uncertainty (%):	
±2	

<5	Noise Equivalent Energy (μJ):
500mJ/cm² (10ns, 1064nm)	Maximum Incident Energy Density:
50μJ - 50mJ	Energy Range:
Physical & Mechanical Properties	
25	Active Area Diameter (mm):
Optical Properties	
1064	Calibration Wavelength (nm):
17	Maximum Pulse Width (μs):
190 - 12000	Wavelength Range (nm):
Sensor	
Pyroelectric	Type of Sensor:
Electrical	
1000	Maximum Repetition Rate (pps):
5	Maximum Incident Beam Power (W):
Hardware & Interface Connectivity	
USB	Connector:
3.0	Length of Cable (m):
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- ISO 17025 Certified
- Embedded Spectral Compensation Characteristics
- Automatic Temperature Compensation

Coherent® EnergyMax Laser Energy Sensors are designed for a variety of demanding laser measurement applications. These energy sensors, available in meter or meterless USB configurations, incorporate a diffuse coating to minimize specular reflection and feature large active areas. The J-50MB-YAG combines the MaxBlack coating with a diffuser for use with high energy lasers of up to 3J. Coherent® EnergyMax Laser Energy Sensors utilize onboard sensors to automate temperature compensation for improved measurement accuracy.