

Pixelink M-Series M12M-CYL Microscopy Monochrome Camera



Stock #17-812 1 In Stock

-

1

+

£3,024^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£3,024.00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

Monochrome	Spectrum:
General	
Monochrome Microscopy Camera	Type:
M12M-CYL	Model Number:
Pixelink	Manufacturer:
	Camera Series:

M-Series	
Physical & Mechanical Properties	
80.88 x 54.01 (excludes lens mount)	Dimensions (mm):
218.5	Weight (g):
Housing:	
Full	
Sensor	
Not Specified	Image Buffer:
1.1"	Sensor Format:
Resolution (Megapixels):	
12.30	
Frame Rate (fps):	
32.50	
Pixels (H x V):	
4,096 x 3,000	
Pixel Size, H x V (µm):	
3.45 x 3.45	
Sensing Area, H x V (mm):	
14.1 x 10.4	
Imaging Sensor:	
Sony IMX253	
Type of Sensor:	
Progressive Scan CMOS	
Shutter Type:	
Global	
Pixel Depth:	
8/12 bit	
Exposure Time:	
Not Specified	
Dynamic Range (dB):	
70	
Machine Vision Standard:	
USB3 Vision	
Electrical	
Power Consumption (W):	
Not Specified	
Hardware & Interface Connectivity	
Interface:	
USB 3.0	
Connector:	
USB 3.0, Micro-B	
Power Supply:	
Power over USB	
GPIOs:	
None	
Synchronization:	
Software Trigger	
Interface Port Orientation:	
Back Panel	
GPIO Connector Type:	
None	
Threading & Mounting	
Mount:	
C-Mount	
Mounting Threads:	
No Mounting Threads/Tripod Adapter	
Environmental & Durability Factors	
Operating Temperature (°C):	
0 to +50	
Storage Temperature (°C):	
-45 to +85	
Regulatory Compliance	
RoHS 2015:	
Compliant	

Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- High Resolution Sensors up to 20 MegaPixel
- Pixelink® Capture Software Included
- Compact Form Factor
- Optional Three-Tier µScope Microscopy Software

Pixelink® M-Series Microscopy Cameras provide cost-effective, high-resolution imaging capabilities for both brightfield and darkfield microscopy. These cameras are designed to capture high resolution images at up to 20MP and are available with various sensor sizes and frame rates. These cameras include a USB 3.0 cable and Pixelink® Capture Software, making it easy to integrate into existing microscopy systems in a variety of laboratory settings. The optional three-tier µScope Microscopy Software (Essentials, Standard, Professional) offers advanced microscopy targeted features and measurement tools such as live measurement, time lapse capture, and live image comparison. Pixelink® M-Series Microscopy Cameras are ideal for demanding applications requiring high resolution and low noise imaging including life science, metrology, and medical imaging.

Note:Pixelink® Capture Software available for download. USB 3.0 cable included.