

## Power Supply for 0.5-0.8mW HeNe Laser, 12 VDC, Bare Wire Leads



L28 Series with CDRH Delay HeNe Laser Power Supply

Stock **#11-382** **20+ In Stock**

⊖ 1 ⊕ £280<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	£280.00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads



### General

OEM **Type:**

**Compatible Laser Models:**  
[1108](#), [1108P](#), [1107](#), [1107P](#)

L23 Series **Model Number:**

**Compatible Laser Stock Number:**  
[#62-714](#), [#62-715](#), [#62-716](#), [#62-717](#)

CDRH Delay (3-5 seconds)

**Features:**

**Physical & Mechanical Properties**

4.00 x 1.50 x 1.00      **Dimensions (inches):**

**Electrical**

5      **Output Power (W):**

2 (Max. Current Draw)      **Input Current (A):**

**Hardware & Interface Connectivity**

1250      **Output Voltage (V):**

4      **Output Current (mA):**

High Voltage Alden Connector      **Connector:**

10-14 DC      **Input Voltage (V):**

**Regulatory Compliance**

[View](#)      **Certificate of Conformance:**

**Product Details**

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

**Note:** Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

**Technical Information**

**Beam Expander Mounting Configurations**

Click on an item below to be brought to that item's product page.

