

[See all 43 Products in Family](#)

Power Supply for 15-22.5mW HeNe Laser, AC, US Plug



Benchtop Power Supply, AC Input (Front)



Stock **#11-391** **9 In Stock**

-

1

+

£864⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£864.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads



General	
Type:	
Benchtop	
Compatible Laser Models:	
1144 , 1144P , 1145P , 1145	
Model Number:	
SL93 Series	

Compatible Laser Stock Number: #62-728, #62-729, #62-731, #62-732	
Turn Key, CDRH Delay (3-5 seconds)	Features:
Physical & Mechanical Properties	
9.00 x 5.50 x 2.38	Dimensions (inches):
Electrical	
24.7	Output Power (W):
0.60/0.30	Input Current (A):
Hardware & Interface Connectivity	
3800	Output Voltage (V):
6.5	Output Current (mA):
High Voltage Alden Connector	Connector:
100/110/220 (AC)	Input Voltage (V):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

