

C8205, APS-C Color, Teledyne DALSA Genie Nano 10GigE PoE Camera

See More by [Teledyne DALSA](#)



Teledyne DALSA Genie™ Nano 10GigE Cameras - Front



Stock **#28-679** [CONTACT US](#)

-

1

+

£5,975⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£5,975.50 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:

Color Camera

G6-GC31-C8205	Model Number:
Teledyne DALSA	Manufacturer:
Genie Nano-10GigE	Camera Series:
Color	Spectrum:
Physical & Mechanical Properties	
59 x 59 x 41 (excludes connectors and lens mount)	Dimensions (mm):
183	Weight (g):
Full	Housing:
Sensor	
APS-C	Sensor Format:
67.10	Resolution (Megapixels):
13.80	Frame Rate (fps):
8,192 x 8,192	Pixels (H x V):
2.50 x 2.50	Pixel Size, H x V (µm):
20.48 x 20.48	Sensing Area, H x V (mm):
Teledyne e2v Emerald 67M	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
8/10 bit	Pixel Depth:
Automatic, Programmable, or via External Trigger	Exposure Time:
62.00	Dynamic Range (dB):
GigE Vision v2.0	Machine Vision Standard:
Electrical	
12.5	Power Consumption (W):
Hardware & Interface Connectivity	
10GigE (PoE)	Interface:
5GigE, RJ45 with Screw Locks	Connector:
2 opto-isolated input, 3 opto-isolated output	GPIOs:
Hardware Trigger (GPIO) or Software Trigger	Synchronization:
Back Panel	Interface Port Orientation:
6-pin Hirose (HR10)	GPIO Connector Type:
Threading & Mounting	
M42-Mount	Mount:
1/4-20 with Tripod Mount Adapter #34-966	Mounting Threads:
Environmental & Durability Factors	
-20 to +60	Operating Temperature (°C):
-30 to +60	Storage Temperature (°C):

Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 235:

PRODUCT DETAILS

- Up to 67.10 MP Resolution with Framerrates up to 18.50FPS
- Supports Trigger-to-Image Reliability (T2IR) Framework
- Compact (44 x 59 x 59mm), M42-Mount, Lightweight, and Robust All Metal Design



Teledyne DALSA Genie™ Nano 10GigE Cameras are designed with the 10GBASE-T (10GigE) Ethernet Interface and can also run at ethernet link speeds of 1, 2.5, or 5GigE. These M42-mount cameras are available with either the Teledyne e2v Emerald 36Msensor featuring a 1.4” format or the Teledyne e2v Emerald 67Msensor which features an APS-C format. Genie™ Nano cameras support Sapera LT SDKs and 3rd Party GenICam compliant SDKs allowing fo upgrading current systems without changing application software. Teledyne DALSA Genie™ Nano 10GigE Cameras support the Trigger-to-Image Reliability (T2IR) framework which is a combination of hardware and software features that work together at a system level to help improve the reliability and reduce the downtime of imaging systems. These cameras are ideal for applications involving Electronics Manufacturing Inspection, Intelligent Traffic Systems, and Aerial Imaging.

Sapera LT is a free image acquisition and control software development toolkit (SDK) for Teledyne DALSA'S 1D cameras / 2D cameras / 3D Laser Profiler cameras and frame grabbers. Hardware independent in nature, Sapera LT offers a rich development ecosystem for machine vision OEMs and system integrators. Sapera LT supports image acquisition from cameras and frame grabbers based on machine vision standards including GigE VSION™, CameraLink®, CameraLink HS™, CoaXpress®, and USB3 VSION™.