

Rodagon C-Mount Adapter



#14-708: Rodagon C-Mount Adapter

Stock **#14-708** 3 In Stock

-

1

+

£69⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£69.00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Lens Adapter

Type:

Optical Properties

VIS

Lens Wavelength Range:

Threading & Mounting

C-Mount

Mount:

Regulatory Compliance		
Compliant	RoHS 2015:	
	View	
View	Certificate of Conformance:	
	Reach 235:	
Compliant		

Product Details

- Up to 174mm Image Circle for Line Scan or Area Scan
- C-Mount, F-Mount, T-Mount Lens
- Up to 1.3 MegaPixels or 8k Line Scan, 7µm Pixel Size Sensors
- 35mm to 135mm Focal Length

Originally designed as enlarging lenses, these high-resolution lenses can accommodate 1" format sensors and larger, which makes them a great choice for line scan cameras. This unmatched adaptability, combined with low distortion and constant resolution over the entire viewable field, makes Rodagon lenses optimal for close focus applications for which they consistently yield higher magnifications and better resolution than standard fixed focal length lenses. This makes them ideal for use with high-resolution cameras.

Lenses have M39 x 1/26" base threading. A Leica Lens Adapter ([#14-705](#) for the 35, 50, 60, 80, and 105mm lenses or [#54-126](#) for the 135mm lens) is required and sold separately to allow attachment to the Modular Focus Tube (MFT). The MFT is required for focusing the lens and for connection to standard camera mounts. The MFT does not ship with a camera adapter; camera adapters for [C-Mount](#), [F-Mount](#), [T-Mount \(M42 x 0.75\)](#), [SLR-mount \(M42 x1.0\)](#), and [M72 x 0.75](#) are available and sold separately. For closer working distances, additional extension tubes can be added (see "Working With Spacers" specification table); values should be used for reference only; choose [#57-791](#) for M72 cameras and [#56-965](#) for all others.

Note: See Technical Image section for spacer length.

Rodagon Modular Focus Tube ([#14-707](#)) and Camera Adapters

To use with a camera, attach a [C-Mount](#), [F-Mount](#), [T-Mount](#), [SLR](#), or [M72](#) adapter (each sold separately) to the [Rodagon Modular Focus Tube](#). Extended range (25mm full stroke) accommodates a range of working distances without requiring spacers. Precision design allows lens to remain centered and unrotatable during focusing. Locking screw included.

Please contact [Applications Engineering](#) for assistance in properly configuring this lens for your application.

Technical Information

Focal Length		25mm of Spacers			50mm of Spacers			75mm of Spacers		
		WD	FOV*	System Mag**	WD	FOV*	System Mag**	WD	FOV*	System Mag**
28mm	min	†			†			†		
	max	†			†			†		
35mm	min	26mm	4mm	66.0X	†			†		
	max	44mm	7.3mm	36.2X	†			†		
50mm	min	78mm	7.4mm	35.7X	56mm	4.7mm	56.2X	†		
	max	155mm	17.3mm	15.3X	77mm	7.4mm	35.7X	†		
60mm	min	153mm	12.7mm	20.8X	99mm	7.0mm	37.7X	78mm	4.9mm	53.9X
	max	655mm	64.7mm	4.1X	153mm	12.7mm	20.8X	99mm	7.0mm	37.7X
80mm	min	580mm	41.9mm	6.3X	226mm	13.9mm	19.0X	156mm	8.3mm	31.8X
	max	∞	4.4°	N/A	580.5mm	41.9mm	6.3X	226mm	13.9mm	19.0X
105mm	min	†			974mm	54.0mm	4.9X	377mm	18.1mm	14.6X
	max	†			∞	3.4°	N/A	974mm	54.0mm	4.9X
135mm	min	†			†			2128mm	95.4mm	2.8X
	max	†			†			∞	2.6°	N/A

*FOV (Field of View) calculated horizontally for 1/2" sensor format
**System Magnification specified for 1/2" sensor format and 13" monitor
† No Image Possible with This Length of Spacers