

[See all 43 Products in Family](#)

Model 1122, 2mW Random Polarization, Lumentum HeNe Laser



Lumentum High Performance Helium-Neon Lasers



Stock **#62-720** CLEARANCE **5 In Stock**

-

 1

+

£1,028⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£1,028.00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads



General	
10	Warm-Up Time (minutes):
Lumentum	Manufacturer:
HeNe	Type of Laser:

IIIa		Laser Class - CDRH:
1122		Model Number:
Physical & Mechanical Properties		
Pointing Stability after Warm Up (mrad/°C): After 15 min: <0.02		
0.92		Weight (lbs):
Length of Laser Head (inches): 10.71		
Static Alignment: Centered to Outer Cylinder: ±0.01" Parallel to Outer Cylinder: ±1.0 mrad		
Pointing Stability (mrad/°C): From Cold Start, 25°: <0.1		
1.74		Diameter of Laser Head (inches):
Optical Properties		
Random		Polarization:
TEM ₀₀		Spatial Mode:
632.80		Wavelength (nm):
±3		Beam Diameter Tolerance (%):
±3		Beam Divergence Tolerance (%):
Mean Power over 8 hrs: ±2.5		Maximum Drift:
0.63		Beam Diameter (mm):
1.30		Beam Divergence (mrad):
Red		Color:
>95%		Mode Purity (TEM ₀₀):
Electrical		
2		Output Power (mW):
30 Hz - 10 MHz 0.1%		RMS Noise:
730		Longitudinal Mode Spacing, Nominal (MHz):
2.0		Minimum Output Power, TEM ₀₀ (mW):
Hardware & Interface Connectivity		
Power Supply: #11-384 (12VDC), #11-385 (24VDC), #11-389 (110/220VAC)		
Free Space		Output Type:
Environmental & Durability Factors		
-40 to +70		Operating Temperature (°C):
0 to 100%, non-condensing		Operating Humidity:
-40 to +150		Storage Temperature (°C):
Regulatory Compliance		
Compliant		RoHS 2015:
View		Certificate of Conformance:
Compliant		REACH 241:

Product Details

110V or 220V power supplies sold separately. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993.

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

