

SCHOTT GG435, 12.5mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-410** 3-4 DAYS

- 1 + **£27.20**

ADD TO CART

Qty 1-10
£27.20
Qty 11+
£23.80
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Cut-On Wavelength (nm):
435.00 ±6

Density (g/cm³): 2.55
Glass/Filter Number: SCHOTT GG435
Coating: Uncoated
Color: Yellow
Passband Limit 1 λ_{p1} (nm): 520
Passband Limit 2 λ_{p2} (nm): 700
Index of Refraction n_d: 1.52
Spectral Transmittance t_p (%): 92
Stopband Limit λ_s(nm): 370
Surface Quality: 60-40
Transformation Temperature (°C): 537
Thickness (mm): 1.00 ±0.1
Type: Longpass Filter
Wavelength: VS
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--