

Schott KL Annular Ring Light 40mm Dia

See More by [SCHOTT Optical Components](#)



Stock **#72-164** **1 In Stock**

-

1

+

£850⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£850.00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

157.04	Model Number:
Brightfield Ring Light	Type:

Note:	
Compatible with objective dia. of 40mm	
Manufacturer:	
SCHOTT	
Geometry:	
Ring Light	
Compatible Product:	
KL 1600 and 2500	
Physical & Mechanical Properties	
Inner Diameter (mm):	
40	
Length (mm):	
1,000.00	
Outer Diameter (mm):	
64	
Optical Properties	
Working Distance (mm):	
25 - 300	
Regulatory Compliance	
Certificate of Conformance:	
View	

PRODUCT DETAILS

- Maximum Light Intensity of 1100 Lumens
- Continuous Dimming from 0 - 100%
- Various Light Guide Options Available
- Ideal for Use with Stereo Microscopes

SCHOTT KL Fiber Optic Light Sources are LED cold light sources that produce intense, but heat free light for microscopy applications. Combining the efficient light output of the light engine with various light guide geometries offers significantly higher intensities compared to direct LED light. Two light source models are available, the KL 1600 which features a 680 lumens maximum intensity and the KL 2500 which features an 1100 lumens maximum intensity with an extra-fine dimming option. SCHOTT KL Fiber Optic Light Sources are ergonomically designed to have a small footprint, allowing them to be easily integrated into compact benchtop lab settings. The uniform light quality of the KL Series is ideal for biological, geological, and pathological stereo microscope applications.

Note: Power cord sold separately.

TECHNICAL INFORMATION

