

## NIST Traceable Midrange Sensor, 280 - 340nm



#88-136 with NIST Traceable Sensor

Stock **#88-138** [CONTACT US](#)

-

1

+

£425<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | £425.00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

| Product Downloads |
|-------------------|
|-------------------|

### SPECIFICATIONS

#### Physical & Mechanical Properties

Accuracy (%):  
±5

#### Optical Properties

Wavelength Range (nm):

280 - 340

310.00

Calibration Wavelength (nm):

Regulatory Compliance

[View](#)

Certificate of Conformance:

PRODUCT DETAILS

- Designed to Detect UV Wavelengths from 250 – 380nm
- NIST Certified Sensors
- 9V Battery Provides up to 120 Hours of Operation
- Requires One NIST Traceable Sensor for Operation

The NIST Certified UV Radiometer is ideal for inspecting ultraviolet light sources in a variety of quality control applications. The NIST Certified UV Radiometer is powered by a standard 9V battery for up to 120 hours of operation. Three NIST certified interchangeable sensors are available to detect a wide range of ultraviolet wavelengths from 250 – 380nm. The NIST Certified UV Radiometer’s range switch allows the selection of three intensity ranges.

**Note:** The UV Radiometer Unit ([#88-136](#)) requires one NIST Traceable Sensor ([#88-137](#), [#88-138](#), or [#88-139](#)) for operation.