

[See all 48 Products in Family](#)

## Norland Optical Adhesive NOA 72, 100g Bottle

See More by [Norland](#)



Norland Optical Adhesive NOA 72, 100g Bottle

Stock **#17-344** **1 In Stock**

⊖ 1 ⊕ £98<sup>40</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | £98.40 each                   |
| Qty 5-11       | £88.56 each                   |
| Qty 12+        | £84.16 each                   |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

| General  |                 |
|----------|-----------------|
| 3.52     | Size (oz):      |
| 72       | Norland Number: |
| 4 months | Shelf Life:     |

Bottle **Type:**

**Typical Applications:**  
Bonding plastics or glass where low UV light transmission prevents curing of other adhesives

UVMS **Cure:**

## Optical Properties

1.56 @ 589nm **Index of Refraction ( $n_d$ ):**

315 - 450 **Absorption Range (nm):**

## Material Properties

Excellent **Glass Bonding:**

Good **Metal Bonding:**

Excellent/Good **Plastic Bonding:**

155 **Viscosity (cps):**

Plastic to Plastic/Glass **Bonding Type:**

5 **Energy for Full Cure ( $J/cm^2$ ):**

## Environmental & Durability Factors

Hard & Resilient **Durability:**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 251:**

## Product Details

- Excellent Optical Qualities
- Adhesives for Glass, Metal, and Plastic Bonding
- Cure Quickly when Exposed to UV Light
- [Preloaded Norland Optical Adhesive Syringes](#) Also Available

Norland Optical Adhesives are clear, solvent-free optical adhesives designed to fully cure in only minutes when exposed to ultraviolet light. These adhesives are used in precision alignment or positioning applications that require a robust and resilient bond. Norland Optical Adhesives feature a variety of bonding types, including but not limited to glass to glass, glass to glass/metal, and plastic to plastic/glass. To use Norland Optical Adhesives, apply the adhesive to the optical surface, position the components, and use a [UV light source](#) to set the components in place. Since the adhesive will not cure until exposed to UV light, time can be taken during the positioning process to perfect product alignment.

## Technical Information

| NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES    |   |
|--|---|
| Title  | Description   |
| <a href="#">Applying Adhesive</a>                    | Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles. |
| <a href="#">Chemical Resistance of NOA</a>           | Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.                        |
| <a href="#">Preventing Lens Separations with NOA</a> | Covers best practices to avoid adhesive failures when bonding optical elements.   |
| <a href="#">Separating Lenses Bonded with NOA</a>    | Covers how to unbond optical elements bonded with Norland Optical Adhesives.  |

