


Normal Response, 16.4mm², Silicon Detector



Silicon Photodiodes

Stock #54-034 3-4 DAYS

- 1 + **£45.90**

ADD TO CART

Qty 1-4
£45.90
Qty 5+
£39.95
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Operating Temperature (°C):
-40 to 100

Type:
Biased

Typical Applications:
High light levels, pulse detectors, AC light measurement

Terminal Capacitance (pF): 330 @ 0 V; 60 @ 10 V
Rise Time (ns): 17 @ -10 V/50 Ω, 632nm
Voltage Bias, V_{Bias} (V): -10
Responsivity @ 970nm (AW): 0.65
Active Area (mm²): 16.4
Noise Equivalent Power NEP (W/ Hz^{1/2}): 1.9 x 10 ⁻¹⁴
Detectivity (cmHz^{1/2}/W): 2.13 x 10 ¹³ @ -10 V, 970nm
Maximum Breakdown Voltage (V): 30.00
Model Number: PIN-6D
Note: Normal Response
Construction: PIN
Outer Diameter (inches): 0.550
Dark Current I_d (nA): 0.5 @ 10V
Length of Leads (inches): 1.50
Protective Window: Borosilicate
Package: TO-8

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View