

NUV-VIS-NIR Nd:YAG Laser Line Vertical Mitutoyo Video Microscope Unit

See More by [Mitutoyo](#)



#89-622 + Objective

Stock **#89-622** 1 In Stock

-

1

+

£6,736^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£6,736.00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

378-507	Model Number:
NUV-VIS-NIR	Range:
Vertical Mount, Brightfield, erect image	Type:

Mitutoyo	Manufacturer:
Compatible Objectives: M Plan Apo/HR/SL and M Plan NIR/NUV	
Note: Magnification: 1X Tube Lens Optional C-Mount adapter #37-044 available for dual-camera system	
Note:	
Physical & Mechanical Properties	
980.00	Weight (g):
Optical Properties	
355, 532, 1064	Design Wavelength DWL (nm):
1X	Magnification:
Sensor	
2/3"	Maximum Sensor Format:
Threading & Mounting	
C-Mount	Mount:
Objective Mounts: M26 x 36 TPI	Mounting Threads:
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

PRODUCT DETAILS

- Designed for use with [Mitutoyo NIR, NUV, and UV Infinity Corrected Objectives](#)
- Maximum Sensor Size up to 2/3"
- Ideal for Laser Processing and Machining applications

Mitutoyo Nd:YAG Laser Line Video Microscope Units (VMU) allow for quick and easy setup of laser processing systems by connecting an infinity corrected objective to a c-mount camera. Optimized for Nd:YAG laser lines of 266, 355, 532, and 1064nm, these VMUs are designed for use with [Mitutoyo UV, NUV, and NIR infinity corrected objectives](#). These VMUs can also be used as infrared inspection systems when using an infrared light source and an infrared camera. Mitutoyo Nd:YAG Laser Line Video Microscope Units (VMU) are ideal for laser processing and imaging applications such as cutting, trimming, and repair of IC wiring, thin-film processing, and infrared spectral characteristic analysis. A dual-camera laser line VMU option is also available for high and low magnification observation.

TECHNICAL INFORMATION

Vertical Laser Line VMU (#89-622)

