

Sealed 450mm White Line Light



Stock **#74-191** NEW **1 In Stock**

-

1

+

£2,588⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£2,588.00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

- Type of Optics:

Collimated
- Type of Illumination:

LED Illuminator

Note:

Compatible with #18-645 external controller	
Advanced Illumination	Manufacturer:
Line Light	
Geometry:	
Constant	
Illumination Mode:	
Physical & Mechanical Properties	
Length (mm):	
450.00	
Dimensions (mm):	
459.8 L x 51.1 W	
Weight (g):	
2163	
Optical Properties	
Color:	
White	
Working Distance (inches):	
0.5-23	
Hardware & Interface Connectivity	
Connector:	
4-pin Male M12	
Operating Voltage (V):	
24VDC, 4.5A	
Power Supply:	
Power Supply Required and Sold Separately: #73-977	
Threading & Mounting	
Mount:	
T-Slot for M6 Nut	
Environmental & Durability Factors	
Operating Temperature (°C):	
0 °C to 35 °C	
Environmental Rating:	
IP67	
Regulatory Compliance	
RoHS 2015:	
Exempt	
Certificate of Conformance:	
View	
Reach 247:	
Contains SVHC(s)	

PRODUCT DETAILS

- IP67 For Dust and Debris Protection
- High Intensity Illumination Profile
- Available in UV, White, Blue, Green, Red, & NIR
- Ideal For Line Scan Applications

The Advanced Illumination Sealed High Intensity Line Lights provide a uniform illumination profile for line scan applications in rugged environments. These lights are IP67-rated for protection against dust, debris, and liquid, offering reliable performance in harsh environments. The lights are available in UV, white, blue, green, red, and NIR wavelengths and are passively cooled for continuous long-term operation. The Advanced Illumination High Intensity Line Lights feature an embedded controller that is designed for continuous operation and housed within the light itself. These lights are ideal for rugged line scan applications including inspection of sheetrock, lumber, and ceramics, and food and beverage washdown environments.