

# Ocean Optics HR6 VIS-NIR High Resolution Spectrometer

See More by [Ocean Optics](#)



Stock #90-029 **NEW** [CONTACT US](#)

⊖ 1 ⊕ £6,262<sup>40</sup>

**ADD TO CART**

#### Volume Pricing

Qty 1+	£6,262.40 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

#### Product Downloads

#### General

OceanDirect & OceanView

**Software:**

7.2 ms – 5 s

**Integration Time:**

HR-6VIS500-25

**Model Number:**

**Note:**  
Includes manual QR code, software QR code,  
calibration reports for wavelength and linearity, 1 m  
USB cable

SMA905	<b>Input Port Termination:</b>
Ruled Diffraction Grating: 600 Grooves/mm, Blazed @ 500nm	<b>Grating:</b>
Cross Czerny Turner	<b>Optical Bench:</b>
<b>Physical &amp; Mechanical Properties</b>	
25	<b>Slit Width (µm):</b>
0.9306	<b>Weight (kg):</b>
149.0 x 106.4 x 48.2	<b>Dimensions (mm):</b>
<b>Optical Properties</b>	
0.57	<b>Spectral Resolution (nm):</b>
400 - 840	<b>Wavelength Range (nm):</b>
<b>Sensor</b>	
CCD	<b>Type of Sensor:</b>
<b>Electrical</b>	
Single Scan @ 10 ms: 400:1 Max per second with High Speed Averaging Mode: 3500:1	<b>Signal to Noise S/N Ratio:</b>
<b>Hardware &amp; Interface Connectivity</b>	
USB, RS-232	<b>Computer Interface:</b>
<b>Threading &amp; Mounting</b>	
(3) 2-56	<b>Mounting Threads:</b>
<b>Environmental &amp; Durability Factors</b>	
0 to +55	<b>Operating Temperature (°C):</b>
-30 to +70	<b>Storage Temperature (°C):</b>
0.02 nm/°C	<b>Thermal Stability:</b>
<b>Regulatory Compliance</b>	
<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 250:</b>

## Product Details

- High Resolution Spectrometers for Narrow Peak Identification
- Spectral Ranges Spanning UV-VIS, VIS-NIR, and NIR Wavelengths
- Rapid Acquisition Speed and Excellent Thermal Stability

Ocean Optics HR High Resolution Spectrometers, available in HR2, HR4, and HR6 models, are designed to identify narrow spectral peaks with detailed spectral analysis for applications that require high-resolution solutions. The HR2 spectrometers feature high-resolution performance, fast scan speeds, and excellent thermal stability, providing rapid, real-time results ideal for applications such as plasma monitoring and pharmaceutical analysis. The HR4 spectrometers combine high-resolution spectral analysis with excellent thermal stability, making these models excel in precision-demanding environments such as DNA/RNA analysis, biomedical research, and high-throughput reflection testing. The HR6 spectrometers offer high sensitivity, high resolution, and excellent signal-to-noise ratio (SNR) performance for applications including protein absorbance and emission of broadband sources. The Ocean Optics HR High Resolution Spectrometers include the user-friendly OceanView software system to optimize spectrometer performance, ease system integration, and access data for analysis.