

Tube Lens



Stock **#18-505** **1 In Stock**

-

1

+

£416⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	£416.00 each
Qty 5+	£395.20 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Note:
One required between camera tube and tube lens

spacer/filter cube

Physical & Mechanical Properties

	Length (mm):
16.15	
	Maximum Diameter (mm):
36	

Optical Properties

	Focal Length FL (mm):
120.00	
	Magnification:
1X	

Threading & Mounting

	Mounting Threads:
M29 x 0.75 & Ø30mm Dovetail	

Regulatory Compliance

	Certificate of Conformance:
View	

PRODUCT DETAILS


- Up to 43% Smaller than Industry Standard Systems
- Optimized Performance up to 1.1" Sensor
- Ideal for Life Science and Industrial Applications
- Winner of the [2023 Bronze VSD Innovators Award](#)

Edmund Optics® 120i Plan APO Infinity Corrected Objectives are infinite conjugate microscope objectives that offer exception image flatness and chromatic correction over 400-700nm. These objectives were designed for a 1.1" sensor to offer a large field of view and reliable image quality for high-throughput imaging applications. Ideal for life science and machine vision applications such as microscopy, flow cytometry, pharmaceutical inspection, and assembly line or fault inspection.

These objectives won the [2023 Bronze VSD Innovators Award](#).

TECHNICAL INFORMATION

Compact Tube Lens System



Standard Tube Lens System

