


WinCamD-LCM Beam Profiler



Stock **#24-211** **1 In Stock**

-

1

+

£5,006⁵⁰

ADD TO CART

Volume Pricing	
Qty 1+	£5,006.50 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

Physical & Mechanical Properties

Dimensions (mm):	
46 x46 x20	
Dimensional Accuracy:	
±1µm	

Optical Properties

Spectral Range:	
355 - 1150	
Minimum Stimulation, Pulsed:	
USB 2.0: 6.3 kHz USB 3.0: 12.6 kHz	
Beam Diameter (µm):	
55 (10 Pixels)	
Sensor	
Pixel Size, H x V (µm):	
5.5 x 5.5	
Pixels (H x V):	
2,048 x 2,048	
Sensing Area, H x V (mm):	
11.3 x 11.3	
Sensor Format:	
1"	
Frame Rate:	
60Hz	
Electrical	
Signal to Noise S/N Ratio (dB):	
2,500:1	
Peak Noise (nW/cm²):	
34 dB optical / 68 dB electrical	
Threading & Mounting	
Mount:	
8-32 thread, 8 mm deep	
Regulatory Compliance	
RoHS 2015:	
Exempt	
Certificate of Conformance:	
View	
REACH 241:	
Contains SVHC(s)	

PRODUCT DETAILS

- Designed for Use from 355 to 1150nm
- Compatible with Beam Diameters Down to 52µm
- Robust and Easy to Use Free Software [Provided](#)
- Measure Beam Wander, M², Divergence, and More

DataRay Beam Profilers provide excellent solutions for beam analysis of both continuous wave and pulsed laser sources. The integrated CMOS sensor eliminates comet trailing for higher resolution output and allows for update rates of 60+ Hz. Sensors are available with active sizes of 6.6, 11.3, and 25mm horizontals, enabling measurement of large beam diameters. DataRay Beam Profilers have the added advantage of a free, robust software with analysis features such as M² measurement, beam wander and logging, and instrument alignment. These profilers are USB3.0/2.0 powered and include a 3m flexible screw locking cable. Neutral density filters with optical densities of 1.0, 2.0, and 4.0 are included.