

# Coherent® Thermopile Power Sensor 1168348 | 300mW - 150W, USB

See More by [Coherent®](#)



Stock #88-414 **5 In Stock**

⊖ 1 ⊕ £1,472<sup>00</sup>

**ADD TO CART**

## Volume Pricing

Qty 1+	£1,472.00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads

## General

**Model Number:**  
PM150-50C  
Coherent Part Number: 1168348

**Type:**  
Meterless

**Calibration Uncertainty (%):**  
±2

1 - 150 Long Pulse Joule Mode Range (J):

Water/Air Cooling Method:

0.6 @ 1064nm, 10ns Maximum Incident Energy Density (J/cm<sup>2</sup>):

## Physical & Mechanical Properties

50 Active Area Diameter (mm):

## Optical Properties

10600 Calibration Wavelength (nm):

190 - 11000 Wavelength Range (nm):

0.19 - 11 Wavelength Range (µm):

## Sensor

Thermopile Type of Sensor:

## Electrical

80 (air-cooled) Maximum Intermittent Power, <5min (W):

6 Maximum Incident Power Density (kW/cm<sup>2</sup>):

300mW - 150W Power Range:

## Hardware & Interface Connectivity

2.5 Length of Cable (m):

USB Computer Interface:

## Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

## Product Details

- Superior Damage Resistance
- Wide Dynamic Range
- ISO 17025 Certified

Coherent® Thermopile Power Sensors are ideal for measuring the average power of continuous wave lasers or pulsed laser energy. Thermopile sensors operate by absorbing and converting incident laser radiation into heat, which then flows to a heat sink. The temperature difference between the absorber and heat sink is converted into an electrical signal by a thermocouple junction. Coherent® Thermopile Power Sensors, unlike semiconductor sensors, do not saturate. Unlike semiconductor sensors, thermopile sensors feature high power capability and flat spectral response.