

[See all 10 Products in Family](#)

Polarizer-Analyzer for Nd:YAG Mitutoyo Video Microscope Unit

See More by [Mitutoyo](#)



Stock **#71-021** [CONTACT US](#)

-

1

+

£1,352⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£1,352.00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Mitutoyo	Manufacturer:
378-513, 378-514	Compatible Objectives:
Provides simplified polarized light observation	Note:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- Designed for use with [Mitutoyo NIR, NUV, and UV Infinity Corrected Objectives](#)
 - Maximum Sensor Size up to 2/3"
 - Ideal for Laser Processing and Machining applications
- Mitutoyo Nd:YAG Laser Line Video Microscope Units (VMU) allow for quick and easy setup of laser processing systems by connecting an infinity corrected objective to a c-mount camera. Optimized for Nd:YAG laser lines of 266, 355, 532, and 1064nm, these VMUs are designed for use with [Mitutoyo UV, NUV, and NIR infinity corrected objectives](#). These VMUs can also be used as infrared inspection systems when using an infrared light source and an infrared camera. Mitutoyo Nd:YAG Laser Line Video Microscope Units (VMU) are ideal for laser processing and imaging applications such as cutting, trimming, and repair of IC wiring, thin-film processing, and infrared spectral characteristic analysis. A dual-camera laser line VMU option is also available for high and low magnification observation.