

SCHOTT BG66, 100 x 80mm, 4.5mm Thick, Matte Plate Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#26-911** **4 In Stock**

-

1

+

£312^{.80}

ADD TO CART

Volume Pricing	
Qty 1-10	£312.80 each
Qty 11+	£276.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Bandpass Filter	Type:
Physical & Mechanical Properties	
100.0 x 80.0	Dimensions (mm):
100.00	Length (mm):

4.50 ±0.5	Thickness (mm):
80.00	Width (mm):
Break Edges	Edges:
Optical Properties	
514.00	Center Wavelength CWL (nm):
SCHOTT BG66	Glass/Filter Number:
Uncoated	Coating:
Blue-Green	Color:
1.54	Index of Refraction (n _d):
NIR Cutoff	Wavelength:
Material Properties	
2.85	Density (g/cm ³):
416	Transformation Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Unpolished Colored Glass Plates
- Large Raw Material Sizes up to 165 x 165mm
- Available in All [SCHOTT Colored Glass Types](#)
- [Polished SCHOTT Colored Glass Filters](#) Also Available

SCHOTT Matte Colored Glass Filter Plates are unpolished plates of colored glass that are used as raw material to manufacture [SCHOTT Colored Glass Filters](#). With large standard sizes up to 165 x 165mm, these plates can be cut, ground, and polished to meet application requirements for a wide range of filter sizes. SCHOTT Matte Colored Glass Filter Plates are available in all [SCHOTT colored glass types](#), including shortpass (heat absorbing), longpass, bandpass, and neutral density. To learn more about how our custom optical colored glass filter capabilities can be used for your application, see our [capabilities page](#).

Quote Your Size