

Silicon Based Touchscreen Portable Laser Power Meter



Silicon Based Touchscreen Portable Laser Power Meter, #34-514

Stock **#34-514** 2 In Stock

-

1

+

£1,648⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	£1,648.00 each
Qty 5+	£1,484.00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
17	Operating Lifetime (hours):
0.2	Response Time (s):
Touch screen color LCD	Type of Display:
USB Port Available for Data Transfer	Note:

Physical & Mechanical Properties	
212.00	Length (mm):
	Weight (g):
150.00	
41.00	Width (mm):
	Depth (mm):
15.0	
7.00	Accuracy (%):

Optical Properties	
320 - 1100	Wavelength Range (nm):
	Spectral Range:
320 - 1100nm (attenuator Off)	
400 - 1100nm (attenuator On)	

Sensor	
10 x 10	Maximum Sensor Size (mm):

Electrical	
36 (attenuator Off) 300 (attenuator On)	Incident Power (mW):
	Maximum Incident Power Density (W/cm²):
100.00	
0.3 nW - 36 mW @ 980nm (attenuator Off) 3 nW - 300 mW @ 980nm (attenuator On)	Power Range:
	Noise Equivalent Power (pW):
10 @ 980nm	

Hardware & Interface Connectivity	
USB Rechargeable Battery	Power Supply:

Threading & Mounting	
8-32 threaded (x1)	Mounting Hole for Screw:

Regulatory Compliance	
Compliant	RoHS 2015:
	Certificate of Conformance:
View	
Compliant	Reach 242:

Product Details

- Small Portable Design with Touchscreen Display
- Computer and Software Not Required
- High Damage Threshold
- USB Rechargeable Battery

Touchscreen Portable Laser Power Meters feature LCD displays with touchscreen controls, the ability to adjust wavelength, brightness and screen orientation, and min/max display. Available in two designs, one as a silicon based sensor and the other an absorber, these portable power meters can transfer data to a computer for data logging via a mini USB port. The silicon sensor model (#34-514) features a folding body design with a click stop at 90 degrees, providing the unique ability of being placed on an optical table unmounted when oriented at 90 degrees. If the beam height is 78mm off the optical table, you can simply set the folded power meter directly onto the table. Both Touchscreen Portable Laser Power Meter models feature 8-32 mounting holes for table top mounting and rechargeable battery.

Note: Mini-USB cable not included.