

Ultra-Thin Polarizer, 1550nm, 10 x 10mm, Uncoated



Ultra-Thin Polarizer, Square

Stock **#26-650** **1 In Stock**

-

1

+

£362⁴⁰

ADD TO CART

Volume Pricing	
Qty 1+	£362.40 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

Physical & Mechanical Properties

10 x 10 +0/-0.1	Dimensions (mm):
0.09 ± 0.025	Thickness (mm):

Optical Properties

Uncoated	Coating:
	Extinction Ratio:

>10,000:1	
Substrate: ☐	
Sodium Silicate Glass Doped with Silver Nanoparticles	
Surface Quality:	
40-20	
Transmission (%):	
>88	
Wavelength Range (nm):	
1500 - 1600	
Damage Threshold, By Design: ☐	
10 W/cm ²	
Acceptance Angle (°):	
± 20°	
Transmitted Wavefront Error, RMS:	
<3 λ	

Environmental & Durability Factors

Operating Temperature (°C):	
-50 to +400	

Regulatory Compliance

RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
REACH 241:	
Compliant	

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- **NEW LOWER PRICE!**
- Lightweight 90µm Thick Substrate
- >10,000:1 Extinction Ratio
- Excellent Resistance to Temperature, Chemicals, and Harsh Environments
- Range of Standard Sizes, Coatings, and Custom Options Available

Ultra-Thin Nanoparticle Polarizers are a lightweight 90µm thick alternative to traditional polarizers while providing a high transmission and an extinction ratio of >10,000:1. Constructed from sodium silicate glass substrate doped with prolate silver nanoparticles, these polarizers provide high temperature stability up to +400°C, chemical resistance, and resistance to UV radiation and bleaching. These polarizers are available uncoated, Single-Side AR coated, or Double-Side AR coated and cover wavelength ranges from 366-1600nm. Ultra-Thin Nanoparticle Polarizers design are ideal for use in telecom, medical, and aerospace applications as well as in optical isolators, polarization interferometry, and improving signal-to-noise ratio.