


Ultra-Thin Polarizer, 1550nm, 25mm Dia, Single-Side AR Coated



Ultra-Thin Polarizer, Circle

Stock **#26-649** 1 In Stock

-

1

+

£1,707²³

ADD TO CART

Volume Pricing	
Qty 1+	£1,707.23 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

Physical & Mechanical Properties

25.00 +0/-0.2

Diameter (mm):

0.09 ± 0.025

Thickness (mm):

Optical Properties	
Single-Side AR	Coating:
>10,000:1	Extinction Ratio:
Sodium Silicate Glass Doped with Silver Nanoparticles	Substrate: ☐
40-20	Surface Quality:
>92	Transmission (%):
Not available	Coating Specification:
1500 - 1600	Wavelength Range (nm):
10 W/cm ²	Damage Threshold, By Design: ☐
± 20°	Acceptance Angle (°):
<3 λ	Transmitted Wavefront Error, RMS:
Environmental & Durability Factors	
-50 to +400	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

PRODUCT DETAILS

- NEW LOWER PRICE!
 - Lightweight 90µm Thick Substrate
 - >10,000:1 Extinction Ratio
 - Excellent Resistance to Temperature, Chemicals, and Harsh Environments
 - Range of Standard Sizes, Coatings, and Custom Options Available
- Ultra-Thin Nanoparticle Polarizers are a lightweight 90µm thick alternative to traditional polarizers while providing a high transmission and an extinction ratio of >10,000:1. Constructed from sodium silicate glass substrate doped with prolate silver nanoparticles, these polarizers provide high temperature stability up to +400°C, chemical resistance, and resistance to UV radiation and bleaching. These polarizers are available uncoated, Single-Side AR coated, or Double-Side AR coated and cover wavelength ranges from 366-1600nm. Ultra-Thin Nanoparticle Polarizers design are ideal for use in telecom, medical, and aerospace applications as well as in optical isolators, polarization interferometry, and improving signal-to-noise ratio.

CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).